

Rollin[®] HiPage plus


Key performance

- High scrolling resistance
- High mechanical resistance
- Slightly positive paper feed
- High carcass stability

MAIN APPLICATION

Coldset

**Rollin Hi-Page Plus is available
in 4-ply, 1,96 mm thickness**



Rollin Hi-Page Plus

✓ The product at a glance

| | |
|--|-------------------------|
| INK COMPATIBILITY | Hybrid |
| PRINTING SURFACE COLOUR | Blue |
| THICKNESS (mm) | 1,96 |
| AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation | 250 |
| SURFACE ROUGHNESS (Ra micron) | 1,0 |
| ELONGATION (%) | <0,9 |
| TENSILE STRENGTH (N/mm) | >75 |
| FEED FEATURES | Slightly positive |
| WATER & SOLVENT PROTECTION | Yes |
| ADDITIONAL INFORMATION | |
| APPLICATION | Premium coldset blanket |

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**