



Rollin[®] Strip



Key performance

- Specifically designed for strippable and varnishing applications
- Smooth varnish laydown
- Easy to strip due to the special compressible layer
- Excellent ink transfer and high resistance to ink pick up
- Suitable for flood, spot, knock out coating applications

MAIN APPLICATION

Coating

Rollin Strip is available in 4-ply, 1,95 mm thickness



Rollin Strip



The product at a glance

TYPE OF VARNISH	Conventional
PRINTING SURFACE COLOUR	Light Blue
THICKNESS (mm)	1,95
SURFACE ROUGHNESS (Ra micron)	0,8
SURFACE	Rubber
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	250
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>60
CARRIER	Fabric
CUTTING DEPTH (mm)	0,6

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**