



# Rollin<sup>®</sup> Contrast Black

## Key performance

- Special top face for both conventional & UV inks
- Very good half tone reproduction and high printing quality
- Excellent paper smash resistance
- Reduced edge mark
- Excellent option when using more UV than conventional inks

## MAIN APPLICATION

Sheetfed

**Rollin Contrast Black is available in 3 ply, 1,95 mm thickness**



**Rollin Contrast Black**



## The product at a glance

<b>INK COMPATIBILITY</b>	Hybrid
<b>PRINTING SURFACE COLOUR</b>	Black
<b>THICKNESS (mm)</b>	1,95
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,23 mm Indentation</b>	250
<b>SURFACE ROUGHNESS (Ra micron)</b>	0,8
<b>ELONGATION (%)</b>	<0,9
<b>TENSILE STRENGTH (N/mm)</b>	>60
<b>ADDITIONAL INFORMATION</b>	
<b>APPLICATIONS</b>	Suitable for alternating printing (conventional & UV inks)

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)**