

# Selection guide

## Printing blankets coating plates

**Sawa<sup>®</sup>** for Asia Pacific



Trelleborg Printing Solutions design and manufacture offset printing blankets and coating plates, for all kind of inks and applications.

Sava printing blankets bring substantial advantages to printers and offer a wide and multi-purpose product range, especially for packaging applications, by reason of a centenary tradition in rubber manufacturing.

### Key technical features

---

SAVA Advantage, the unique product line with **cord technology**

**ISEGA** certificates, a safety warranty for printers

**UV technology**, for HUV and LED UV press requirements

Specific offer for **coating** with UV and aqueous

#### FEATURING

- Reduced gage loss
- High smash resistance
- Longer service life
- Excellent print quality

#### FEATURING

- Pollutant-free materials
- No health and food safety risk
- Extra value for the food packaging industry and for consumer goods

#### FEATURING

- Strong chemical resistance
- First class solids and halftone reproduction
- No ink back-trapping
- Excellent smash and edge mark resistance

#### FEATURING

- Easy preparation and cleaning
- Easier strip with visible cut lines
- Simpler handling
- Enhance print quality
- Accelerate printing productivity



## Coldset

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	COMPRESSIBILITY (Mpa @ 0.17mm Indentation)	SURFACE ROUGHNESS	CONSTRUCTION	WATER & SOLVENT PROTECTION	ELONGATION (% @ 10N/mm)
PRIVILEGE OPAL	HYBRID	GREEN	1,96	0.8	1.7	TEXTILE CARCASS	YES	<1.2

## Web Heatset

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	COMPRESSIBILITY (Mpa @ 0.17mm Indentation)	SURFACE ROUGHNESS	CONSTRUCTION	WATER & SOLVENT PROTECTION	ELONGATION (% @ 10N/mm)
ADVANTAGE PEARL	HYBRID	TURQUOISE GREEN	1,95	0.9	1.2	CORD CARCASS	YES	<0.7
PRIVILEGE TOPAZ	HYBRID	TURQUOISE GREEN	1,70 and 1,96	0.9	1.2	TEXTILE CARCASS	YES	<1.2

## Sheetfed & Packaging

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	COMPRESSIBILITY (Mpa @ 0.17mm Indentation)	SURFACE ROUGHNESS	CONSTRUCTION	WATER & SOLVENT PROTECTION	ELONGATION (% @ 10N/mm)
ADVANTAGE PLUS	CONVENTIONAL	BLUE	1,95	0.8	0.8	CORD CARCASS	YES	<0.7
ADVANTAGE PEARL	HYBRID	TURQUOISE GREEN	1,95	0.9	1.2	CORD CARCASS	YES	<0.7
ADVANTAGE DUAL	HYBRID	INDIGO	1,95	0.8	0.9	CORD CARCASS	YES	<0.7
PRIVILEGE	CONVENTIONAL	BLUE	1,70 and 1,96	0.8	0.8	TEXTILE CARCASS	YES	<1.2

## UV Sheetfed & Packaging

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	COMPRESSIBILITY (Mpa @ 0.17mm Indentation)	SURFACE ROUGHNESS	CONSTRUCTION	WATER & SOLVENT PROTECTION	ELONGATION (% @ 10N/mm)
ADVANTAGE UV RED	UV	RED	1,95	0.9	1.1	CORD CARCASS	YES	<0.7
PRIVILEGE UV BLACK	HYBRID	BLACK	1,96	0.9	1.1	TEXTILE CARCASS	YES	<1.2

## Coating

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	RELIEF mm	CARRIER	COATING SURFACE	SHORE A	STRIPPABLE
STRIP 4 DUAL	AQUEOUS	DARK GREY	1.15/1.35/1.95/2.15/2.35	0,80-1,15	POLYESTER	RUBBER	82	YES, NO FABRICS
ADVANTAGE STRIPPING	AQUEOUS	PINK	1,70 and 1,95	0,80 / 0,90	CORD PLY	RUBBER	82	YES
ADVANTAGE UV STRIPPING JOY	UV	APRICOT	1,95	0,90	CORD PLY	RUBBER	82	YES

## Metal Decorating

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	COMPRESSIBILITY (Mpa @ 0.17mm Indentation)	SURFACE ROUGHNESS	CONSTRUCTION	WATER & SOLVENT PROTECTION	ELONGATION (% @ 10N/mm)
PRIVILEGE	CONVENTIONAL	BLUE	1,70 and 1,96	0.8	0.8	TEXTILE CARCASS	YES	<1.2
PRIVILEGE TOPAZ	HYBRID	TURQUOISE GREEN	1,70 and 1,96	0.9	1.2	TEXTILE CARCASS	YES	<1.2
PRIVILEGE UV BLACK	UV	BLACK	1,96	0.9	1.1	TEXTILE CARCASS	YES	<1.2

## Business Forms and Envelopes

STYLE NAME	INK COMPATIBILITY	SURFACE COLOR	THICKNESS mm	COMPRESSIBILITY (Mpa @ 0.17mm Indentation)	SURFACE ROUGHNESS	CONSTRUCTION	WATER & SOLVENT PROTECTION	ELONGATION (% @ 10N/mm)
PRIVILEGE	CONVENTIONAL	BLUE	1,70 and 1,95	0.8	0.8	TEXTILE CARCASS	YES	<1.2
PRIVILEGE UV BLACK	UV	BLACK	1,96	0.9	1.1	TEXTILE CARCASS	YES	<1.2
SLB E-FORM	HYBRID	GREY	0,95 and 1,07	1.1	1.6	ADHESIVE	STICKY BACK	n/a



Trelleborg Printing Solutions is a leading global supplier of unique customer solutions for polymer-coated fabrics deployed in offset, flexo and digital printing applications.

Vulcan®, Rollin®, Printec® and Sava® are brand leaders, providing offset printing blankets for newspapers, magazines and catalogues, business forms, metal decorating and packaging markets plus a wide range of printing blankets for special printing machines.

Trelleborg printing blankets are suitable for all kind of inks: conventional, hybrid and UV.

[WWW.TRELLEBORG.COM/PRINTING](http://WWW.TRELLEBORG.COM/PRINTING)

[printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)

<https://www.linkedin.com/company/trelleborg-printing-solutions>

<https://twitter.com/PrintingInsight>

Darja Pangrič  
Sales Area Manager SAVA, APAC  
Mobile +386 30 464 191  
[darja.pangric@trelleborg.com](mailto:darja.pangric@trelleborg.com)



The information contained in this document is intended to provide guidance. The information is NOT a specification and all figures in the document are nominal. This document and the information it contains do not create any warranties for any product and Trelleborg Printing Solutions disclaims any warranty of merchantability or fitness for a particular purpose for the product described in this document. This document discloses information that is proprietary to Trelleborg Printing Solutions. The receipt or possession of the document does not confer any right to reproduce or disclose the document, any information contained in it, or any physical article or device, or to practice any method or process except by written agreement with Trelleborg Printing Solutions. Trelleborg Printing Solutions is committed to the ongoing development of its products. For that reason, Trelleborg Printing Solutions reserves the right to alter the actual specifications of its products without prior notice.