



Key performance

- Specifically designed for strippable and varnishing applications
- Smooth varnish laydown
- Easy to strip due to the special compressible layer
- Excellent ink transfer and high resistance to ink pick up
- Suitable for flood, spot, knock out coating applications

MAIN APPLICATION

Coating

Vulcan 714 Strip is available in 4 ply, 1,96 mm thickness



Vulcan 714 Strip

✓ The product at a glance

TYPE OF VARNISH	Conventional
PRINTING SURFACE COLOUR	Light Blue
SURFACE	Rubber
THICKNESS (mm)	1,96
CARRIER	Fabric
CUTTING DEPTH (mm)	0,6
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	0,8
ELONGATION (%)	<0,9
TENSILE STRENGTHS (N/mm)	>59

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**