



vulcan 202

Key performance

- High mechanical resistance
- Designed with **Feed-0 Technology**:
 - Optimum paper feed tension
 - Reduced risks of paper breaks
 - Easier control of colour register during the start-up
 - Improved paper wastage control

MAIN APPLICATION

Coldset

**Vulcan 202 is available in 4-ply,
1,96 mm thickness**



Vulcan 202



The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Green
THICKNESS (mm)	1,96
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	1,0
FEED FEATURES	Neutral
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>75
WATER & SOLVENT PROTECTION	Yes
NEW TECHNOLOGY	Feed-0
ADDITIONAL INFORMATION	
PRESS FEATURES	FEED-0 no pack version available

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**