



Key performance

- Specifically designed to absorb the mechanical vibrations caused by new generation of printing presses
- Implements all benefits of the **Dynatech System**:
 - Better vibration absorption
 - Less gears streaking marks
 - Higher paper smash resistance
 - Blanket consistency
 - Excellent reboundability

MAIN APPLICATION

Heatset

Vulcan Techno is available in 3 ply, 1,70 mm thickness.



Vulcan Techno

✓ The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Green
THICKNESS (mm)	1,70
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	230
SURFACE ROUGHNESS (Ra micron)	0,8
FEED FEATURES	Positive
ELONGATION (%)	<0,9
TENSILE STRENGTHS (N/mm)	>60
WATER & SOLVENT PROTECTION	Yes
ADDITIONAL INFORMATION	
APPLICATIONS	DYNATECH, perfect choice for 16pp

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**