



Key performance

- Specifically designed for a wide range of applications in sheetfed printing and in metal decorating
- Suitable for high volumes printing
- Improved printing quality in tough conditions

MAIN APPLICATION

Commercial Sheetfed

Vulcan Eco is available in 4 ply, 1,96 mm thickness



Vulcan Eco

✓ The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,96
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	300
SURFACE ROUGHNESS (Ra micron)	1,0
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>59
ADDITIONAL INFORMATION	
APPLICATIONS	Vulcan print quality on a variety of stocks

FOR ANY FURTHER DETAILS AND FOR A QUOTATION PLEASE REFER TO YOUR SALES MANAGER OR EMAIL US AT: printingsm@trelleborg.com