

Printec® 336

Key Performance

- Sticky back blanket (adhesive-backed) for UV inks
- High print quality
- Resistance to chemical absorption and embossing
- Increased blanket lifetime
- Suitable for labels and envelopes printing
- Adhesive: clean and easy removal from the cylinder

MAIN APPLICATION

2-piece can

**Printec 336 is available in 3 ply
(1,90/1,93/1,95 mm) thickness**



Printec 336



The product at a glance

INK COMPATIBILITY	UV
PRINTING SURFACE COLOUR	Orange
THICKNESS (mm)	1,90 (1336) / 1,93 (2336) / 1,95 (3336)
AVERAGE LOAD VALUE N/cm ² @ 0,20 mm Indentation	115
SURFACE ROUGHNESS (µm)	0,70 to 1,30
ELONGATION (%)	< 2
TENSILE STRENGTHS (kgf/cm)	> 58
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
APPLICATIONS	Business Forms and Labels

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printing@trelleborg.com**