



# Printec® 700

## Key performance

- Suitable for Heatset and Newspaper
- High print quality
- Calibrated thickness
- Positive paper feed

## MAIN APPLICATION

Web Applications

**Vulcan 700 Master is available in 4-ply, 1,71/1,96 mm thickness.**



700

## ✓ The product at a glance

<b>INK COMPATIBILITY</b>	Conventional
<b>PRINTING SURFACE COLOUR</b>	Light Blue
<b>THICKNESS (mm)</b>	1,70 / 1,96
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,23 mm Indentation</b>	260
<b>SURFACE ROUGHNESS (Ra micron)</b>	1,0
<b>FEED FEATURES</b>	Positive
<b>ELONGATION (%)</b>	<0,9
<b>TENSILE STRENGTHS (N/mm)</b>	>60
<b>WATER &amp; SOLVENT PROTECTION</b>	Yes
<b>ADDITIONAL INFORMATION</b>	
<b>BLANKET CONSTRUCTION</b>	High compressibility for high speed presses

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printing@trelleborg.com](mailto:printing@trelleborg.com)**