



Printec 815

Key performance

- Ideal for packaging printing and metal decorating, 4-color presses
- Excellent half tone reproduction and ink transfer
- High edge marking resistance
- Increased blanket lifetime

MAIN APPLICATION

Packaging,
Metal Decorating

**Printec 815 is available in
3 ply, 1,95 mm thickness.**



Printec 815



The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,95
AVERAGE LOAD VALUE N/cm ² @ 0,23 mm Indentation	400
SURFACE ROUGHNESS (Ra micron)	1,4
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
DESIGN	Specifically designed for metal decorating applications

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**