



vulcan[®] Royal Form

Key performance

- Sticky back blanket
- High print quality
- High edge marking resistance
- Increased blanket lifetime
- Suitable for labels and envelopes printing
- Adhesive: clean and easy removal from the cylinder

MAIN APPLICATION

Business Forms, Labels

Vulcan Royal Form is available in 2 ply, 0,90 - 0,95 - 1,00 - 1,05 mm thickness.



Vulcan Royal Form

✓ The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Light Blue
THICKNESS (mm)	0,90 - 0,95 - 1,00 - 1,05
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	300
SURFACE ROUGHNESS (Ra micron)	0,8
ELONGATION (%)	<0,7%
TENSILE STRENGTHS (N/mm)	>55
WATER & SOLVENT PROTECTION	N/A
ADDITIONAL INFORMATION	
APPLICATIONS	UV inks version available (Royal Form UV)

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**