

# Printec® 640-B

## Key Performance

- Ideal for newspaper high speed presses
- Designed with Feed-0 Technology: optimum paper feed tension; reduced risks of paper breaks; easier control of colour register during the start-up; improved paper wastage control

## MAIN APPLICATION

Newspaper Coldset

**Printec 640-B is available in 4 ply 1,96 mm thickness**



**Printec 640-B**

## ✓ The product at a glance

<b>INK COMPATIBILITY</b>	Hybrid
<b>PRINTING SURFACE COLOUR</b>	Blue
<b>THICKNESS (mm)</b>	1,96
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,20 mm Indentation</b>	250
<b>SURFACE ROUGHNESS (µm)</b>	1,0
<b>ELONGATION (%)</b>	< 0,9
<b>TENSILE STRENGTH (N/mm)</b>	>75
<b>WATER &amp; SOLVENT PROTECTION</b>	Yes
<b>ADDITIONAL INFORMATION</b>	
<b>APPLICATIONS</b>	Newspaper and 4 ply web

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)**