

Rollin® Hi-page plus

Key performance

- High scrolling resistance
- High mechanical resistance
- Slightly positive paper feed
- High carcass stability

MAIN APPLICATION

Coldset

Rollin Hi-Page Plus is available in 4-ply, 1,95 mm thickness.



Rollin Hi-Page Plus



The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,95
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	1,0
ELONGATION (%)	<0,9
TENSILE STRENGTHS (N/mm)	>70
FEED FEATURES	Slightly positive
WATER & SOLVENT PROTECTION	Yes
ADDITIONAL INFORMATION	
APPLICATION	Low stretch carcass for double width presses

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**