



# Rollin<sup>®</sup> Hi-page plus

## Key performance

- High scrolling resistance
- High mechanical resistance
- Slightly positive paper feed
- High carcass stability

## MAIN APPLICATION

Heatset, Coldset

**Rollin Hi-Page Plus is available in 4-ply, 1,95 mm thickness.**



**Rollin Hi-Page Plus**



## The product at a glance

<b>INK COMPATIBILITY</b>	Hybrid
<b>PRINTING SURFACE COLOUR</b>	Blue
<b>THICKNESS (mm)</b>	1,95
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,23 mm Indentation</b>	250
<b>SURFACE ROUGHNESS (Ra micron)</b>	1,0
<b>ELONGATION (%)</b>	<0,9
<b>TENSILE STRENGTHS (N/mm)</b>	>70
<b>FEED FEATURES</b>	Slightly positive
<b>WATER &amp; SOLVENT PROTECTION</b>	Yes
<b>ADDITIONAL INFORMATION</b>	
<b>APPLICATION</b>	Ideal for newspaper printing

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)**