



Rollin[®] Synchro

Key performance

- Durability Combined with Excellent Printing due to the unique carcass
- Implements all benefits of the **Dynatech System**:
 - Better vibration absorption
 - Less gears streaking marks
 - Higher paper smash resistance
 - Blanket consistency and high performance
 - Excellent rebondaubility

MAIN APPLICATION

Coldset

Rollin Synchro is available in 3-ply, 1,95 mm thickness



Rollin Synchro

✓ The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Light blue
THICKNESS (mm)	1,95
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	1,0
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>67
WATER & SOLVENT PROTECTION	Yes
FEED FEATURES	Positive
ADDITIONAL INFORMATION	
ADVANCED TECHNOLOGY	Dynatech System

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**