


## Key performance

- High scrolling and high mechanical resistance
- Designed with **Feed-0 Technology**:
  - Optimum paper feed tension
  - Reduced risks of paper breaks
  - Easier control of colour register during the start-up
  - Improved paper wastage control

## MAIN APPLICATION

Newspaper Coldset

Vulcan 202 is available in 4-ply,  
1,95 mm thickness



Vulcan 202

## ✓ The product at a glance

<b>INK COMPATIBILITY</b>	Hybrid
<b>THICKNESS (mm)</b>	1.95
<b>PRINTING SURFACE COLOUR</b>	Green
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,23 mm Indentation</b>	250
<b>SURFACE ROUGHNESS (Ra micron)</b>	1,0
<b>FEED FEATURES</b>	Neutral
<b>ELONGATION (%)</b>	<0,9
<b>TENSILE STRENGTH (N/mm)</b>	>75
<b>WATER &amp; SOLVENT PROTECTION</b>	Yes
<b>ADDITIONAL INFORMATION</b>	
<b>ADVANCED TECHNOLOGY</b>	Feed-0

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)**