



Key performance

- Ideal for 2-color presses
- Excellent print quality
- Optimum half tone reproduction
- High edge marking resistance

MAIN APPLICATION

Metal decorating

Vulcan Deco is available in 3-ply, 1,96 mm thickness



Vulcan Deco

✓ The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,96
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	650
SURFACE ROUGHNESS (Ra micron)	1,4
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>60

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**