



Key performance

- Specifically designed for currency printing and metal printing
- Perfect solid printing and ink transfer
- Suitable for fine details reproduction
- Very robust carcass to provide stability on press

MAIN APPLICATION

Currency Printing, Security

Vulcan Solid is available in 3 ply, 1,70 mm thickness.



Vulcan Solid

✓ The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Light Blue
THICKNESS (mm)	1,70
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	Non compressible blanket
SURFACE ROUGHNESS (Ra micron)	1,2
ELONGATION (%)	<0,9%
TENSILE STRENGTHS (N/mm)	>150
WATER & SOLVENT PROTECTION	Yes
ADDITIONAL INFORMATION	
APPLICATIONS	Micro Buffed printing surface finishing

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**