



vulcan[®] Royal Web


Key performance

- High scrolling resistance
- High mechanical resistance
- Slightly positive paper feed
- High carcass stability

MAIN APPLICATION

Newspaper Coldset, Heatset

Vulcan Royal Web available in 4 ply, 1,95 mm thickness.



Vulcan Royal Web

✓ The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,95
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	1,0
FEED FEATURES	Slightly Positive
ELONGATION (%)	<0,9
TENSILE STRENGTHS (N/mm)	>70
WATER & SOLVENT PROTECTION	Yes
ADDITIONAL INFORMATION	
APPLICATIONS	No pack version available

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**