



# Orca

RESILIENT - MEDIUM INTENSITY APPLICATIONS

**Main Benefits**

- **Block tread design**  
Large footprint lowers stress and maximizes tire life.
- **Enhanced stability**  
Faster load positioning and cornering.
- **Energy efficiency**  
Low rolling resistance for improved energy efficiency.
- **Shock absorbance**  
Tire absorbs shock from obstacles.

**Polymer Engineering, Application Expertise**

Trelleborg strives to deliver optimum performance for all our customers. We offer problem-solving products in our premium range. Contact our application specialists to learn more about our latest tire solutions.



STABILITY



TIRE LIFE



BATTERY LIFE



OVERHEATING TIRE



VIBRATION



TIRE CRACKING



EXPLOSION RISK



TIRE CHUNKING

**Special compounds available**





Size	Alternative Size	Rim	Tire type & Compound availability ● STD ■ LOC ▼ BOTH		Product Dimensions [mm]		Load Capacity [kg]		
			Multi Purpose	Non Marking	Overall Diameter	Section Width	Other	Counterbalanced Lift Trucks up to 25 km/h	
							Static	Load Wheel	Steering Wheel
4.00-8		3.00D-8	▼	▼	398	94	1,100	950	730
15x4½-8	125/75-8	3.00D-8	▼	▼	373	110	1,210	1,040	800
5.00-8		3.00D-8	▼	▼	452	114	1,650	1,415	1,090
16x6-8	150/75-8	4.33R-8	▼	▼	409	143	1,740	1,495	1,150
18x7-8	180/70-8	4.33R-8	▼	▼	445	147	2,490	2,145	1,650
140/55-9	15x5.5-9	4.00E-9	▼	▼	380	132	1,360	1,170	900
6.00-9		4.00E-9	▼	▼	520	130	2,190	1,885	1,450
21x8-9	200/75-9	6.00E-9	▼	▼	51=4	180	3,200	2,755	2,120
6.50-10		5.00F-10	▼	▼	568	153	2,720	2,340	1,800
200/50-10		6.50F-10	▼	▼	450	175	2,870	2,470	1,900
23x9-10	225/75-10	6.50F-10	▼	▼	574	187	4,000	3,445	2,650
7.00-12		5.00S-12	▼	▼	646	163	3,380	2,920	2,240
23x10-12	250/60-12	8.00G-12	▼	■	570	219	4,380	3,770	2,900
27x10-12	250/75-12	8.00G-12	▼	▼	670	235	4,530	3,900	3,000
7.00-15	29x8-15	5.5-15	▼	▼	717	162	4,115	3,545	2,725
7.50-15		6.5-15	▼	▼	743	186	4,530	3,900	3,000
8.25-15		6.5-15	▼	▼	803	192	5,510	4,750	3,650
28x9-15	225/75-15 (8.15-15)	7.0-15	▼	▼	680	200	4,530	3,900	3,000
250-15	250/70-15	7.0-15	▼	▼	709	206	5,510	4,750	3,650
250-15	250/70-15	7.5-15	▼	■	709	206	5,510	4,750	3,650
300-15	315/70-15	8.0-15	▼	▼	807	244	6,795	5,850	4,500
355/65-15	32x12½-15 (350-15)	9.75-15	▼	■	809	260	9,060	7,800	6,000



## TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.  
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy  
Phone: +39 0774 384701 - Fax: +39 0774 384702  
[www.trelleborg.com/wheels](http://www.trelleborg.com/wheels)



[facebook.com/Trelleborgmaterialhandling](https://facebook.com/Trelleborgmaterialhandling)

Download the App for free



Tire brochure