



# SR940. Designed for life.



**GET THE MOST OUT OF YOUR TIRES.  
DESIGNED FOR MAXIMUM TIRE LIFE AND BEST COST PER HOUR.**



Download the App for free The Brochure

# SR940 Designed for life.

- 1 Unique tread pattern:**  
Extra wide contact area to maximize tire life and stability
- 2 Side circumferential rib:**  
Great handling and traction performance in wet conditions
- 3 Reinforced sidewall:**  
Excellent stability during loading and unloading operations
- 4 Extra-deep tread:**  
Superior tire life and best cost per hour



\* TPMS: tire pressure management system  
visit [trelleborg.com/wheels](http://trelleborg.com/wheels) for more information

## SR940 MAXIMUM INTENSITY

<b>Tire size</b>	<b>480/95 R 25</b>
<b>Service description LI/SS</b>	208 A5
<b>Permitted rims</b>	13.00/2.5-25 11.25/2.0-25
<b>Overall diameter - new [mm]</b>	1565
<b>Rolling circumference - [mm]</b>	4872
<b>Tread depth [mm]</b>	51
<b>Tread pattern</b>	SR 940
<b>Index of tire strength</b>	***
<b>Type (tubeless/tube type)</b>	TL
<b>Section width - new [mm]</b>	469
<b>Loaded static radius [mm]</b>	683
<b>EAN code</b>	8059971597202

Speed [km/h]	Tire load capacity [kg]				
	Tire pressure [kPa]				
	800	850	900	950	1000
0 Static	16,500	17,350	18,150	19,000	19,800
1 Creep	16,500	17,350	18,150	19,000	19,800
5	16,500	17,350	18,150	19,000	19,800
10	16,500	17,350	18,150	19,000	19,800
15	16,500	17,350	18,150	19,000	19,800
20	16,500	17,350	18,150	19,000	19,800
25	15,000	15,750	16,500	17,250	18,000
30	14,450	15,150	15,900	16,600	17,350
35	13,900	14,550	15,250	15,950	16,650



## TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.  
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy  
Phone: +39 0774 384701 - Fax: +39 0774 384702  
[www.trelleborg.com/wheels](http://www.trelleborg.com/wheels)

[facebook.com/TrelleborgMaterialhandling](https://facebook.com/TrelleborgMaterialhandling)  
[youtube.com/TrelleborgMaterialhandling](https://youtube.com/TrelleborgMaterialhandling)

