



TRELLEBORG

Implement Standard

Implement metric tyre for trailers, spreaders, balers, ploughs, drills
Higher load capacity and higher permitted speed (40-50 kph) than previous version
Low rolling resistance on road transport
Rounded shoulder and tread design for a soft ground contact

Trelleborg Implement Standard.

Technical specifications

Size	LI/SS	Tread Pattern	New tyre		Tyre in service		SLR mm +/- 2%	RC mm +/- 2%	Rim	Tube
			OD mm +/- 1,5%	SW mm +/- 1,5%	OD (max) mm	SW (max) mm				
200/95-12 TL (replaces 7.00-12)	101A8 89A8		684	198	711	213	307	2038 2052	4.25	7.00-12
260/90-13 TL (replaces 9.00-13)	121A8 109A8		795	262	831	279	347 362	2369 2394	6.00F	9.00-13
260/70-15.3 TL (replaces 10.0/75-15.3)	116A8 104A8		760	274	778	279	332 354	2265 2309	9.00	10.0/75-15.3
260/70-15.3 TL (replaces 10.0/75-15.3)	126A8 114A8		760	274	778	279	326 354	2272 2309	9.00	10.0/75-15.3
260/70-15.3 TL (replaces 10.0/75-15.3)	131A8 119A8		760	274	778	279	330 354	2280 2309	9.00	10.0/75-15.3
300/80-15.3 TL	123A8 111A8		900	300	913	305	390 403	2685 2691	9.00-15.3	
300/80-15.3 TL	132A8 120A8		900	300	910	303	393 407	2685 2704	9.00-15.3	
300/80-15.3 TL (replaces 11.5/80-15.3)	132A8 120A8		870	296	902	319	372 407	2595 2642	9.00	11.5/80-15.3
300/80-15.3 TL (replaces 11.5/80-15.3)	141A8 129A8		870	300	902	319	380 407	2610 2642	9.00	11.5/80-15.3
320/80-15.3 TL (replaces 12.5/80-15.3)	145A8 133A8		897	322	936	345	396 424	2691 2702	9.00	12.5/80-15.3
180/90-16 TL (replaces 6.00-16)	100A8 88A8		728	175	753	192	307 337	2162 2194	4.00E	6.00-16
190/90-16 TL (replaces 6.50-16)	108A8 96A8		746	192	772	205	331 343	2223 2245	4.50E	6.50/7.00-16
200/90-16 TL (replaces 7.00-16)	111A8 99A8		764	204	792	213	338 354	2227 2305	5.00F	6.50/7.00-16
210/95-16 TL (replaces 7.50-16)	120A8 108A8		802	218	833	231	347 373	2392 2420	5.50F	7.50-16
260/70-16 TL (replaces 10.5/65-16)	134A8 122A8		776	265	796	279	336 348	2328 2303	W8 (W9)	10.5/65-16
340/55-16 TL (replaces 13.0/55-16)	140A8 128A8		777	342	807	370	333 364	2331 2340	11.00	13.0/55-16
360/65-16 TL (replaces 14.0/65-16)	148A8 136A8		880	362	907	386	377 396	2640 2674	11.00	
360/70-16 TL (replaces 13.0/75-16)	137A8 125A8		905	362	946	386	380 412	2697 2730	11.00	13.0/75-16 14.0/65-16
380/55-17 TL	138A8 125A8		845	384	880	410	355 378	2521 2550	12.00	15.0/55-17
480/45-17 TL	146A8 134A8		868	478	894	517	369 390	2593 2590	16.00	19.0/45-17 500/50-17
520/50-17 TL	159A8 147A8		952	516	988	557	404 421	2820 2855	16.00	

Inches Sizes

10.0/80-12 TL	8 PR 8 PR		716	268	730	277	314	2138	9.00 7.00	8.50-12 10.0/80-12
10.0/80-12 TL	10 PR 10 PR		716	268	730	277	314	2138	9.00 7.00	8.50-12 10.0/80-12



Trelleborg Wheel Systems S.p.A.

Registered office and head office: Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (Roma)

Trade office: Resolution Road, Flagstaff 42, Ashby de la Zouch, Leicestershire, LE65 1DW

Tel. +44 (0)0845 60 11 082 - Fax +44 (0)1530 56 56 30

www.trelleborg.com/wheelsystems - www.trelleborg.com/wheelsystems_uk