

Wheels and rims for light service tyres

The Trelleborg range of wheels and rims, is available from 3" to 16" in size and can be supplied in many different configurations depending on application, requirements for load capacity and several other values influencing the design. The wheels and rims are designed with different specifications – ie. sizes, integral hubs, bearings, bores, offsets, plate thickness, paint finish etc. that match the performance requirements defined.

Rims and wheels available

The table contains the product range available in term of dimensions, widths and configurations. The columns welded/divided indicate whether the specific size of rim/wheel is available as welded version and/or as assembled version. While the columns hub/bore indicate if the size (dimension/width) is available as wheel (hub) and/or rim (bore).

Rim/Wheel width	Dimension	Welded	Divided	Hub	Bore
1.50-3D	3 Inches		●	●	
2.10AX4	4 Inches	●		●	
2.10-4D	4 Inches		●	●	
2.50-4D	4 Inches		●	●	
2.75AX4	4 Inches	●		●	
6.35-4D	4 Inches		●	●	
3.00AX5	5 Inches	●		●	
2.50AX6	6 Inches	●		●	
2.50AX6	6 Inches	●			●
2.50-6D	6 Inches		●		●
3.25-6D	6 Inches		●		●
3.50AX6	6 Inches	●		●	
3.50AX6	6 Inches	●			●
3.50-6D	6 Inches		●		●
4.00AX6	6 Inches	●		●	
4.50AX6	6 Inches	●		●	
4.50AX6	6 Inches	●			●
4.50-6D	6 Inches		●	●	
4.50-6D	6 Inches		●		●
7.00AX6	6 Inches	●		●	
1.40-8D	8 Inches		●		●
2.125-8D	8 Inches		●	●	
2.125-8D	8 Inches		●		●
2.50AX8	8 Inches	●		●	
2.50AX8	8 Inches	●			●
2.50C-8D	8 Inches	●	●		●
3.00DX8	8 Inches	●		●	
3.00DX8	8 Inches	●			●
3.00D-8D	8 Inches		●	●	
3.00D-8D	8 Inches		●		●
3.75I-8D	8 Inches		●		●
4.25I-8D	8 Inches		●		●
4.33R-8D	8 Inches		●		●
4.375X8	8 Inches	●		●	
4.375X8	8 Inches	●			●
5.375-8D	8 Inches		●	●	



Rim/Wheel width	Dimension	Welded	Divided	Hub	Bore
5.375X8	8 Inches	●		●	
5.375X8	8 Inches	●			●
5.50-8D	8 Inches		●		●
5.50AX8	8 Inches	●		●	
5.50AX8	8 Inches	●			●
7.00IX8	8 Inches	●		●	
7.00IX8	8 Inches	●			●
7.00-8D	8 Inches		●		●
8.50AX8	8 Inches	●			●
4.00EX9	9 Inches	●		●	
4.00EX9	9 Inches	●			●
4.00-9D	9 Inches		●	●	
4.00-9D	9 Inches		●		●
6.00E-9D	9 Inches		●		●
3.00BX10	10 Inches	●			●
3.50IX10	10 Inches	●		●	
3.50IX10	10 Inches	●			●
5.00F-10	10 Inches		●	●	
5.00F-10	10 Inches		●		●
5.50F-10	10 Inches		●		●
5.50F-10	10 Inches		●	●	
6.00IX10	10 Inches	●		●	
6.00IX10	10 Inches	●			●
6.00-10	10 Inches		●		●
7.00IX10	10 Inches	●			●
8.25IX10	10 Inches	●			●
8.50IX10	10 Inches	●			●
3.00IX12	12 Inches	●		●	
3.00IX12	12 Inches	●			●
4.00IX12	12 Inches	●		●	
4.00IX12	12 Inches	●			●
4.25IX12	12 Inches	●		●	
4.25IX12	12 Inches	●			●
5.00S-12	12 Inches		●		●
7.00IX12	12 Inches	●		●	
7.00IX12	12 Inches	●			●
9.00IX12	12 Inches	●		●	
9.00IX12	12 Inches	●			●
8.50IX12	12 Inches	●			●
10.50IX12	12 Inches	●			●
4.50IX13	13 Inches	●		●	
5.50EX14	14 Inches	●		●	
5.50EX14	14 Inches	●			●
6.00JX14	14 Inches	●			●
6.75X14.5	14.5 Inches	●		●	
6.75X14.5	14.5 Inches	●			●
3.00JX15	15 Inches	●			●
4.00JX15	15 Inches	●		●	
4.00JX15	15 Inches	●			●
4.50JX15	15 Inches	●		●	
4.50JX15	15 Inches	●			●
5.00JX15	15 Inches	●			●
5.50JX15	15 Inches	●		●	
6.00JX15	15 Inches	●			●
9.00X15	15 Inches	●		●	
10.00LBX15	15 Inches	●			●
13.00LBX15	15 Inches	●			●
4.00EX16	16 Inches	●			●
5.50EX16	16 Inches	●			●
9.00EX16	16 Inches	●		●	

