

# T410 Agroforest. The Flexible Solution.



# T410 Agroforest

T410 Agroforest represents the best choice for both agricultural and forestry application. It guarantees optimal performance in tough forestry service as well as in field use, where comfort and traction are required.

- Reinforced sidewall to guarantee minimum impact and perforation
- Special lug shape to ensure excellent grip and traction in tough terrain
- High level of stability during heavy applications thanks to the shoulder design
- Larger lug contact area if compared to an ordinary tractor pattern



| SIZE                          | LI / SI      | Tread Pattern          | New tyre |       | Tyre in service |             | SLR mm | RC mm | SRI | Rim                    | Tube    |
|-------------------------------|--------------|------------------------|----------|-------|-----------------|-------------|--------|-------|-----|------------------------|---------|
|                               |              |                        | SW mm    | OD mm | SW (max) mm     | OD (max) mm |        |       |     |                        |         |
| <b>320/85-24</b><br>(12.4-24) | 127A8 (124B) | <b>T410 Agroforest</b> | 325      | 1165  | 345             | 1192        | 546    | 3462  | 545 | W9-W10- <b>W11</b>     | 12.4-24 |
| <b>380/85-24</b><br>(14.9-24) | 137A8 (134B) | <b>T410 Agroforest</b> | 380      | 1260  | 410             | 1302        | 583    | 3768  | 590 | W11- <b>W12</b> -W13   | 14.9-24 |
| <b>380/85-28</b><br>(14.9-28) | 139A8 (136B) | <b>T410 Agroforest</b> | 380      | 1365  | 410             | 1403        | 637    | 4071  | 640 | W11- <b>W12</b> -W13   | 14.9-28 |
| <b>420/85-28</b><br>(16.9-28) | 144A8 (141B) | <b>T410 Agroforest</b> | 440      | 1435  | 451             | 1475        | 669    | 4275  | 670 | W13-W14L- <b>W15L</b>  | 16.9-28 |
| <b>420/85-30</b><br>(16.9-30) | 145A8 (142B) | <b>T410 Agroforest</b> | 440      | 1470  | 451             | 1526        | 686    | 4428  | 695 | W13-W14L- <b>W15L</b>  | 16.9-30 |
| <b>460/85-30</b><br>(18.4-30) | 150A8 (147B) | <b>T410 Agroforest</b> | 480      | 1550  | 491             | 1598        | 720    | 4632  | 695 | W14L-W15L- <b>W16L</b> | 18.4-30 |
| <b>420/85-34</b><br>(16.9-34) | 147A8 (144B) | <b>T410 Agroforest</b> | 440      | 1575  | 451             | 1628        | 736    | 4734  | 745 | W13L-W14L- <b>W15L</b> | 16.9-34 |
| <b>460/85-34</b><br>(18.4-34) | 152A8 (149B) | <b>T410 Agroforest</b> | 475      | 1645  | 491             | 1700        | 766    | 4938  | 775 | W14L-W15L- <b>W16L</b> | 18.4-34 |
| <b>420/85-38</b><br>(16.9-38) | 149A8 (146B) | <b>T410 Agroforest</b> | 440      | 1680  | 451             | 1729        | 787    | 5037  | 795 | W13-W14L- <b>W15L</b>  | 16.9-38 |
| <b>460/85-38</b><br>(18.4-38) | 154A8 (151B) | <b>T410 Agroforest</b> | 470      | 1750  | 491             | 1801        | 819    | 5241  | 825 | W14L-W15L- <b>W16L</b> | 18.4-38 |
| <b>520/85-38</b><br>(20.8-38) | 160A8 (157B) | <b>T410 Agroforest</b> | 520      | 1850  | 557             | 1911        | 859    | 5547  | 870 | <b>DW16L</b> -DW18L    | 20.8-38 |



**TRELLEBORG**

Trelleborg Wheel Systems Italia S.p.A.  
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy  
Phone: +39 0774 384701 - Fax: +39 0774 384702  
[www.trelleborg.com/wheels](http://www.trelleborg.com/wheels)

