



T418 Skidder. The Solution for Maximum Traction.



T418 Skidder

T418 is specifically designed for log skidding service with maximum cut and tear resistance, to provide longer tyre life under the most severe operating conditions.

The armored plies and steel belt protect the carcass against stumps, boulders and rocks.

- The perfect solution for heavy-duty skidding logging service
- Maximum cut, tear resistance for longer life time
- Deep and strong lugs that provide and maximize traction and strong grip
- Extra reinforced sidewall increases the stability and protection against impact



SIZE	PR	Tread Pattern	New tyre		Tyre in service		SLR mm	RC mm	Rim	Tube
			SW mm	OD mm	SW (max) mm	OD (max) mm				
23.1-26	16 PR	T418 FS SB	600	1615	615	1655	740	4810	DW20B	23.1-26 TR218
28L-26	20 PR	T418 FS SB	705	1630	725	1670	747	4855	DW25B	28L-26 TR218
24.5-32	16 PR	T418 FS SB	630	1825	645	1870	832	5425	DH21	24.5-32 TR218
30.5L-32	20 PR	T418 FS SB	760	1840	780	1885	840	5470	DH27	30.5-32 TR218
30.5L-32	26 PR	T418 FS SB	760	1840	780	1885	840	5470	DH27	30.5-32 TR218
35.5L-32	24 PR	T418 FS SB	In preparation							

SB = Steelbelt



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheelsystems

