

TM100. Enrich your farming.



TM100

Narrow radial tire, specifically designed for row crop working and highly regarded for delivering comfort.

High Load Capacity

The casing construction and the materials used guarantee high load capacity and exceptional resistance to tire fatigue.

Excellent Traction

The high lug angle ensures traction in all soil conditions from wet to dry.

Superior self-cleaning

The geometry of the lugs and mud breakers give the tire superior self-cleaning characteristics.

Outstanding productivity

The TM100 range, identified by its rounded shoulders, allows working between rows of crops without damaging the plants.



SIZE	Tread Pattern	SW mm	OD mm	SLR mm	RC mm	SRI	Rim	Permitted Rims	Type	Tube
230/95R32 128A8 (128B)	TM100	235	1265	595	3900	600	W7	W6	TUBELESS	9.5-32 TR218
270/95R32 136A8 (136B)	TM100	280	1345	635	4075	625	W9	W10 - W8	TUBELESS	12.4-32 TR218
230/95R36 130A8 (130B)	TM100	235	1365	645	4210	650	W7	W6	TUBELESS	9.5-36 TR218
270/95R38 140A8 (140B)	TM100	285	1480	697	4505	700	W10	W8 - W9	TUBELESS	
210/95R44 120A8 (120B)	TM100	210	1530	725	4670	725	W7	W6	TUBELESS	8.3/9.5-44 TR218
230/95R44 134A8 (134B)	TM100	235	1570	735	4850	750	W7	W8	TUBELESS	8.3/9.5-44 TR218
270/95R44 142A8 (142B)	TM100	270	1645	770	5020	775	W8	W9 - W10	TUBELESS	9.5-44 TR218
300/95R46 148A8 (148B)	TM100	310	1755	840	5400	825	W10	W9 - W11	TUBELESS	12.4-46
230/95R48 136A8 (136B)	TM100	238	1673	780	5170	800	W7	W8	TUBELESS	9.5-48
270/95R48 144A8 (144B)	TM100	275	1750	830	5350	825	W8	W9 - W10	TUBELESS	11.2-48
380/90R50 151A8 (151B)	TM100	390	1945	890	5885	975	W12	W11 - W13	TUBELESS	
300/95R52 151A8 (151B)	TM100	315	1905	890	5805	925	W10	W9 - W11 - DW10 - DW11	TUBELESS	
380/90R54 152A8 (152B)	TM100	380	2040	940	6175	1025	W12	W11 - W13	TUBELESS	



TRELLEBORG



Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels