

Twin Implement Versatility at first sight.



Download the App for free



Tire iBrochure

Twin Implement

Complete range of low ground pressure tires suited for agricultural machines in heavy and severe applications.

SIZE	LI / SS	Tread Pattern	New tire		Tire in service		SLR mm	RC mm	Rim	Type
			SW mm	OD mm	SW (max) mm	OD (max) mm				
280/60-15.5	115A8 103A8		260	730	275	747	325 335	2142 2163	AG8.00	TUBELESS
280/60-15.5	125A8 113A8		272	736	278	747	331	2194	AG8.00	TUBELESS
280/60-15.5	128A8		260	730	275	747	325	2142	AG8.00	TUBE TYPE
400/60-15.5	145A8 132A8		400	875	436	907	384 396	2568 2594	AG13.00	TUBELESS
400/60-15.5	148A8 136A8		410	875	436	907	384 396	2568 2594	AG13.00	TUBELESS
400/60-15.5	145A8		400	875	436	907	384	2598	AG13.00	TUBELESS
420/55-17	133A8 121A8		415	898	420	912	397 404	2667 2685	13.00	TUBELESS
400/55-17.5	131A8 119A8		400	880	420	902	388 400	2583 2609	AG11.75	TUBE TYPE
400/55-22.5	147A8 135A8		400	1000	420	1021	450 460	3035 3045	AG11.75	TUBELESS
500/45-22.5	146A8 134A8		500	1020	528	1042	450 465	3020 3050	AG16.00	TUBELESS
500/60-22.5	155A8 143A8		500	1170	528	1200	500 530	3490 3510	AG16.00	TUBELESS
500/60-22.5	155A8 143A8		500	1170	528	1200	525 545	3490 3510	AG16.00	TUBELESS
560/45-22.5	154A8 142A8		540	1075	609	1111	475 490	3235 3245	AG16.00	TUBELESS
560/60-22.5	158A8 145A8		564	1235	609	1291	525 541	3675 3685	AG16.00	TUBELESS
560/60-22.5	167A8 155A8		564	1235	609	1291	525 541	3675 3685	AG16.00	TUBELESS
600/50-22.5	156A8 144A8		610	1170	638	1214	520 540	3460 3500	AG20.00	TUBELESS
600/50-22.5	156A8 144A8		600	1170	630	1214	520 540	3460 3500	AG20.00	TUBELESS
NEW 600/50-22.5	165A8 153A8		610	1170	638	1214	510 530		AG20.00	TUBELESS
600/50-22.5	168A8 156A8		610	1170	638	1214	500		AG20.00	TUBELESS
710/40-22.5	158A8 146A8		710	1160	773	1179	510 525	3460 3470	AG24.00	TUBELESS
400/60-26.5	147A8 135A8		400	1160	425	1187	525 540	3470 3490	AG13.00	TUBE TYPE
500/60-26.5 *	159A8 147A8		500	1260	528	1289	560 580	3790 3810	AG16.00	TUBELESS
600/55-26.5	166A8 154A8		620	1360	638	1379	595 619	3970 4000	AG20.00	TUBELESS
600/55-26.5	166A8 154A8		600	1350	638	1379	595 619	3970 4000	AG20.00	TUBELESS
710/45-26.5	169A8 157A8		710	1350	773	1384	600 620	3980 4000	AG24.00	TUBELESS
710/45-26.5	169A8 157A8		710	1350	773	1384	590 610	3970 4020	AG24.00	TUBELESS
800/40-26.5	172A8 159A8		800	1350	840	1379	590 610	3970 4020	AG28.00	TUBELESS
800/40-26.5	172A8 159A8		800	1350	840	1379	600 620	3970 4010	AG28.00	TUBELESS
600/60-30.5 *	171A8 159A8		620	1500	638	1536	655 680	4420 4450	AG20.00	TUBELESS
650/65-30.5	173A8 161A8		660	1650	697	1679	710 740	4830 4860	AG20.00	TUBELESS
710/50-30.5	175A8 163A8		727	1500	773	1534	650 680	4425 4455	AG24.00	TUBELESS
710/50-30.5	175A8 163A8		730	1500	773	1534	660 690	4425 4455	AG24.00	TUBELESS
750/60-30.5	178A8 166A8		750	1650	804	1738	710 740	4830 4870	AG24.00	TUBELESS
800/45-30.5	178A8 166A8		800	1500	862	1545	650 670	4455 4485	AG28.00	TUBELESS
800/45-30.5	178A8 166A8		800	1500	840	1536	660 680	4420 4460	AG28.00	TUBELESS
850/50-30.5	179A8 167A8		850	1650	920	1684	691 723	4840 4880	AG28.00	TUBELESS

* Subject to availability



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels

