



MPX TB Multi Purpose Bias Tire

PREMIUM CONSTRUCTION PNEUMATIC

The Trelleborg MPX TB range is designed for telehandler and compact loader applications in the most demanding environments, providing improved traction, better wear resistance and greater stability on all ground surfaces. The unique lug design delivers excellent self-cleaning and grip on muddy surfaces.


Now available with increased load capacity for heavy duty applications, the MPX TB is also ECE 106 approved to meet European safety regulations.

Main Benefits

- Increased load index for heavy-duty applications
- Improved traction with the new lug shape




Applications



TELEHANDERS COMPACT WHEEL LOADERS

Tire Features



EXCELLENT WEAR RESISTANCE ROBUST SIDEWALL IMPROVED TRACTION GREATER STABILITY

MPX TB

PREMIUM CONSTRUCTION PNEUMATIC

Size	Tread Pattern	Rim (Permitted)	OD (mm)	SW (mm)	LSD (mm)	RC (mm)	Service Description LI/SS	Tire Load Capacity (Kg) at Speed (Km/h)							Tire Pressure (bar)
								Static	10	10 Cyc.	20	30	40	50	
400/70-20 IND (REPLACES 405/70-20 & 16/70-20)	MPX TB TL	13 x 20 (13 x 20SDC)	1081	408	493	3294	155A8/B	6065	3295	3955	2875	2740	2635	2635	3,20
								6510	3535	4245	3085	2940	2830	2830	3,50
								7310	3975	4770	3465	3305	3180	3180	4,00
								8115	4410	5290	3845	3665	3525	3525	4,50
								8915	4845	5815	4225	4030	3875	3875	5,00
400/70-24 IND (REPLACES 405/70-24 & 16/70-24)	MPX TB TL	13 x 24 (13 x 24SDC)	1174	410	537	3551	158A8/B	6645	3615	4335	3150	3005	2890	2890	3,20
								7135	3880	4655	3385	3225	3105	3105	3,50
								8015	4360	5230	3800	3625	3485	3485	4,00
								8895	4835	5800	4220	4020	3870	3870	4,50
								9775	5315	6375	4635	4420	4250	4250	5,00
400/80-24 IND (15.5/80-24)	MPX TB TL	DW13 X 24 (DW14L X 24) (DW13L X 24)	1253	410	572	3825	162A8	7430	4040	4845	3520	3360	3230	2940	3,20
								7975	4335	5200	3780	3605	3470	3155	3,50
								8960	4870	5845	4250	4050	3895	3545	4,00
								9940	5405	6485	4715	4495	4325	3935	4,50
								10925	5940	7125	5180	4940	4750	4325	5,00
460/70-24 IND (17.5L-24)	MPX TB TL	DW15L X 24 (DW14L X 24) (DW16L X 24)	1257	455	564	3813	159A8	6540	3555	4265	3100	2960	2845	2585	2,40
								7450	4050	4860	3530	3365	3240	2945	2,80
								8355	4540	5450	3960	3775	3630	3305	3,20
								8960	4870	5845	4245	4050	3895	3540	3,50
								10065	5470	6565	4770	4550	4375	3980	4,00
500/70-24 IND* (19.5L-24)	MPX TB TL	DW16L X 24 (DW15L X 24) (W15L X 24) (W16L X 24)	n.a.	n.a.	n.a.	n.a.	164A8	7475	4065	4875	3545	3380	3250	2960	2,40
								8510	4625	5550	4035	3850	3700	3365	2,80
								9545	5190	6225	4525	4315	4150	3775	3,20
								10235	5565	6675	4850	4630	4450	4050	3,50
								11500	6250	7500	5450	5200	5000	4550	4,00

* in preparation



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels

