



EMR 1040 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability while the multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for loaders and suitable for articulated dumper applications, the EMR 1040 range is the best solution for intensive loading applications in industries such as open pits and quarries as well as infrastructure and building construction and landscaping.

Main Benefits

- Supreme traction in sand and gravel
- Excellent tire life due to deep tread
- High cut resistance



Applications



LOADERS



ARTICULATED DUMP TRUCKS

Tire Features



RADIAL CONSTRUCTION



REINFORCED CARCASS



MULTI SURFACE



EXCELLENT RIDE COMFORT

EMR 1040

PREMIUM RADIAL PNEUMATIC

LOADER/TRANSPORT SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (mm)	Service Description LI/SS Loader/Transport	Tire Load Capacity (kg) at 10 (Km/h)	Tire Pressure (bar)	Tire Load Capacity (kg) at 50 (Km/h)	Tire Pressure (bar)
23.5 R 25	L4/E4	19.50/2.5-25	60	** 201 A2/185 B	14,500	5.75	9,250	4.50
26.5 R 25	L4/E4	22.00/3.0-25	60	** 209 A2/193 B	18,500	5.75	11,500	4.50
29.5 R 25	L4/E4	25.00/3.5-25	65	** 216 A2/200 B	22,400	5.75	14,000	4.50

*/** – Index of tire strength



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels

