



EMR 1042 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability while the multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for articulated dumper and suitable for loader applications, our EMR 1042 tire is the best choice for haulage operations in open pits and quarries and also suitable for infrastructure and building construction and landscaping.

Main Benefits

- Supreme traction in sand and gravel
- Excellent tire life due to deep tread
- High comfort



Applications



ARTICULATED DUMP TRUCKS



LOADERS

Tire Features



RADIAL CONSTRUCTION



REINFORCED CARCASS



MULTI SURFACE



EXCELLENT RIDE COMFORT

EMR 1042

PREMIUM RADIAL PNEUMATIC

TRANSPORT/LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (mm)	Service Description LI/SS Transport/Loader	Tire Load Capacity (kg) at 10 (Km/h)	Tire Pressure (bar)	Tire Load Capacity (kg) at 50 (Km/h)	Tire Pressure (bar)
29.5 R 25	E4/L4	25.00/3.5-25	60	** 200 B/216 A2	22,400	5.75	14,000	4.50

*/** – Index of tire strength



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels

