



ECONOMY MATERIALS HANDLING RESILIENT

## **ECOSOLID** **Pneumatic Shaped Solid**

Ecosolid is an entry-level solid tire option available in the 8" to 15" size range.

Ecosolid is designed for use on forklifts in light-duty application.

### **FEATURES**

- Available in standard black compounds
- Steel-reinforced base
- Wear indicator built in to lug design

\*Testing results concluded from TWS field-testing program.

ECONOMY MATERIALS HANDLING RESILIENT

# ECOSOLID

Tire Size	Alternative Size	Rim Size	LOC	Tire Dimensions (in)		Load Capacity (lbs)			Weight (lbs)
				Overall Diameter	Section Width	Static	Forklift Trucks up to 15 mph		
							Load Wheel	Steering Wheel	
<b>15x4½-8</b>	125/75-8	3.00D-8	•	14.6	4.1	2,670	2,295	1,765	18
<b>5.00-8</b>		3.00D-8	•	18.0	4.8	3,640	3,120	2,405	31
<b>16x6-8</b>	150/75-8	4.33R-8	•	16.1	5.6	3,835	3,295	2,535	31
<b>18x7-8</b>	180/70-8	4.33R-8	•	17.7	5.6	5,490	4,730	3,640	40
<b>140/55-9</b>	15x½-9	4.00E-09	•	14.6	5.0	3,000	2,580	1,985	21
<b>6.00-9</b>		4.00E-09	•	20.0	5.5	4,830	4,155	3,195	52
<b>21x8-9</b>	200/75-9	6.00E-09	•	20.0	7.3	7,055	6,075	4,675	69
<b>6.50-10</b>		5.00F-10	•	22.0	6.4	5,995	5,160	3,970	72
<b>200/50-10</b>		6.50F-10	•	17.6	7.3	6,325	5,445	4,190	46
<b>23x9-10</b>	225/75-10	6.50F-10	•	22.5	7.5	8,820	7,595	5,840	90
<b>7.00-12</b>		5.00S-12	•	26.0	6.6	7,450	6,435	4,940	94
<b>23x10-12</b>	250/60-12	8.00G-12	•	22.5	8.8	9,655	8,310	6,395	99
<b>27x10-12</b>	250/75-12	8.00G-12	•	25.8	9.1	9,985	8,600	6,615	146
<b>8.25-15</b>		6.5-15	•	31.0	8.1	12,145	10,470	8,045	166
<b>28x9-15</b>	225/75-15 (8.15-15)	7.0-15	•	27.0	8.0	8,820	7,595	5,840	118
<b>250-15</b>	250/70-15	7.0-15	•	28.0	8.5	12,145	10,460	8,045	134
<b>300-15</b>	315/70-15	8.0-15	•	32.0	10.0	14,980	12,895	9,920	223
<b>355/65-15</b>	32x12½-15 (350-15)	9.75-15	•	31.9	11.0	19,975	17,195	13,230	251

**AVAILABLE COMPOUNDS**



Standard Black

**TREAD PATTERNS**



Ecosolid

Dealer Logo

Dealer Address and contact information



TRELLEBORG.COM/WHEELS