



Reliability in the shape of a tyre

MID-RANGE MATERIALS HANDLING RESILIENT

MASTERSOLID

Mastersolid is designed to deliver good performance at a competitive price.

Mastersolid delivers a good total value of ownership. It's made from quality rubber compounds, has low rolling resistance, which reduces fuel costs and a wide tread pattern for good stability.

Mastersolid is available in most common sizes in both LOC and NON LOC and in Non-Marking.

PERFORMANCE DEFINED

TYRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tyre life, **additional hours of usage**, reduced downtime and lower maintenance costs.

ENERGY SAVING

Trelleborg is a **leading approved tyre manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

STABILITY

Trelleborg products are designed to have **large footprints** maximizing the contact area, leading to better stability and even tyre wear.

COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and keep noise to a **minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

MASTERSOLID

Tyre Size	Alternative Size	Rim Size	LOC	Tyre Dimensions [mm]		Load Capacity [kg]		
				Overall Diameter	Section Width	Static	Forklift trucks up to 25 km/h	
							Load Wheel	Steering Wheel
3.00-4 *		2.10-4		250	83	295	255	195
3.00-4 *		2.50C-4		250	83	295	255	195
4.00-8		3.00D-8	•	404	104	1100	950	730
15x4½-8	125/75-8	3.00D-8	•	377	104	1210	1040	800
5.00-8		3.00D-8	•	459	115	1650	1415	1090
16x6-8	150/75-8	4.33R-8	•	407	132	1740	1495	1150
18x7-8	180/70-8	4.33R-8	•	454	145	2490	2145	1650
140/55-9	15x5.5-9	4.00E-09	•	380	132	1360	1170	900
6.00-9		4.00E-09	•	519	131	2190	1885	1450
21x8-9	200/75-9	6.00E-09	•	523	168	3200	2755	2120
6.50-10		5.00F-10	•	574	148	2720	2340	1800
200/50-10		6.50F-10	•	456	186	2870	2470	1900
23x9-10	225/75-10	6.50F-10	•	584	210	4000	3445	2650
7.00-12		5.00S-12	•	650	162	3380	2920	2240
23x10-12	250/60-12	8.00G-12	•	581	228	4380	3770	2900
27x10-12	250/75-12	8.00G-12	•	672	228	4530	3900	3000
7.00-15	29x8-15	5.5-15	•	725	186	4115	3545	2725
7.50-15		5.5-15	•	755	187	4530	3900	3000
7.50-15		6.5-15		755	187	4530	3900	3000
8.25-15		6.5-15	•	823	202	5510	4750	3650
28x9-15	225/75-15 (8.15-15)	7.0-15	•	681	202	4530	3900	3000
250-15	250/70-15	7.0-15	•	720	210	5510	4745	3650
250-15	250/70-15	7.5-15		720	210	5510	4745	3650
300-15	315/70-15	8.0-15	•	822	250	6795	5850	4500
465/55-20		16.0-20		1029	465	13590	10800	9000

SPECIAL COMPOUNDS AVAILABLE



* Only available with Military tread pattern

TREAD PATTERNS



MS

