



MID-RANGE MATERIALS HANDLING RESILIENT

## MASTERSOLID

### Reliability in the Shape of a Tire

Mastersolid is designed to deliver good performance at a competitive price.

Mastersolid delivers a good total value of ownership. It's made from quality rubber compounds, has low rolling resistance, which reduces fuel costs and a wide tread pattern for good stability.

Mastersolid is available in most common sizes in both LOC and NON LOC and in Non-Marking.

## PERFORMANCE DEFINED

### TIRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.

### ENERGY SAVING

Trelleborg is a **leading approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

### STABILITY

Trelleborg products are designed to have **large footprints** maximizing the contact area, leading to better stability and even tire wear.

### COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and keep noise to a **minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

MID-RANGE MATERIALS HANDLING RESILIENT

# MASTERSOLID

Tire Size	Alternative Size	Rim Size	LOC	Tire Dimensions (in)		Load Capacity (lbs)			Weight (lbs)
				Overall Diameter	Section Width	Static	Forklift trucks up to 15 mph		
							Load Wheel	Steering Wheel	
<b>3.00-4 *</b>		2.10-4		9.8	3.3	650	560	430	8
<b>3.00-4 *</b>		2.50C-4		9.8	3.3	650	560	430	8
<b>4.00-8</b>		3.00D-8	•	15.9	4.1	2,425	2,095	1,610	24
<b>15x4½-8</b>	125/75-8	3.00D-8	•	14.8	4.1	2,670	2,295	1,765	19
<b>5.00-8</b>		3.00D-8	•	18.1	4.5	3,640	3,120	2,405	34
<b>16x6-8</b>	150/75-8	4.33R-8	•	16.0	5.2	3,835	3,295	2,535	35
<b>18x7-8</b>	180/70-8	4.33R-8	•	17.9	5.7	5,490	4,730	3,640	44
<b>140/55-9</b>	15x5.5-9	4.00E-09	•	15.0	5.2	3,000	2,580	1,985	22
<b>6.00-9</b>		4.00E-09	•	20.4	5.2	4,830	4,155	3,195	56
<b>21x8-9</b>	200/75-9	6.00E-09	•	20.6	6.6	7,055	6,075	4,675	71
<b>6.50-10</b>		5.00F-10	•	22.6	5.8	5,995	5,160	3,970	77
<b>200/50-10</b>		6.50F-10	•	18.0	7.3	6,325	5,445	4,190	51
<b>23x9-10</b>	225/75-10	6.50F-10	•	23.0	8.3	8,820	7,595	5,840	108
<b>7.00-12</b>		5.00S-12	•	25.6	6.4	7,450	6,435	4,940	100
<b>23x10-12</b>	250/60-12	8.00G-12	•	22.9	9.0	9,655	8,310	6,395	105
<b>27x10-12</b>	250/75-12	8.00G-12	•	26.5	9.0	9,985	8,600	6,615	153
<b>7.00-15</b>	29x8-15	5.5-15	•	28.5	7.3	9,070	7,815	6,010	134
<b>7.50-15</b>		5.5-15	•	29.7	7.4	9,985	8,600	6,615	152
<b>7.50-15</b>		6.5-15	•	29.7	7.4	9,985	8,600	6,615	157
<b>8.25-15</b>		6.5-15	•	32.4	8.0	12,145	10,470	8,045	203
<b>28x9-15</b>	225/75-15 (8.15-15)	7.0-15	•	26.8	8.0	9,985	8,600	6,615	124
<b>250-15</b>	250/70-15	7.0-15		28.3	8.3	12,145	10,460	8,045	149
<b>250-15</b>	250/70-15	7.5-15	•	28.3	8.3	12,145	10,460	8,045	152
<b>300-15</b>	315/70-15	8.0-15	•	32.4	9.8	14,980	12,895	9,920	253
<b>465/55-20</b>		16.0-20		40.5	18.3	29,960	23,810	19,840	684

**SPECIAL COMPOUNDS AVAILABLE**



Non-Marking

\* Only available with Military tread pattern

**TREAD PATTERNS**



MS

Dealer Logo

---

Dealer Address and contact information



**TRELLEBORG**

TRELLEBORG.COM/WHEELS