



When only the best will do

PREMIUM RADIAL INDUSTRIAL PNEUMATIC

TR-900

The TR-900 is Trelleborg’s radial option for industrial applications. Designed to withstand today’s demanding applications and modern equipment, the TR-900 offers better stability, traction and security with its unique tread pattern and reinforced sidewalls as compared to a conventional tyre.

The TR-900 is ideal for applications with long runs. The radial construction allows for higher speed and a reduced heat build-up which helps to extend the life of the tyre.



PERFORMANCE DEFINED

TYRE LIFE

Trelleborg products guarantee **the best wear** performance in the industry. This results in longer tyre life, **additional hours of usage**, reduced downtime and lower maintenance costs.

ENERGY SAVING

Trelleborg is a **leading approved tyre manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

STABILITY

Trelleborg tyres are designed with **exceptional stability**. Our tyres are engineered to ensure **proper distribution of heat** and to prevent excessive deflection under load.

COMFORT

Trelleborg recognizes the importance of a **safe working environment**. Our products are designed to minimize vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

TR-900

Tyre Size	Alternative Size	Rim Size	Tyre Dimensions [mm]			Inflation Pressure [bar]	Tyre Type	Load Capacity [kg]	
			Overall Diameter	Section Width	Tread Depth			Forklift trucks up to 25 km/h	
								Load Wheel	Steering Wheel
5.00R8		3.00D-8	468	137	25	10.00	Tube Type	1415	1090
6.00R9		4.00E-09	540	162	25	10.00	Tube Type	1885	1450
6.50R10		5.00F-10	585	180	27	10.00	Tube Type	2340	1800
7.00R12		5.00S-12	670	190	28	10.00	Tube Type	2915	2240
7.00R15	29x8R15	5.5-15	736	195	28	10.00	Tube Type	3540	2725
8.25R15		6.5-15	838	232	32	10.00	Tube Type	4745	3650
28x9R15	225/75R15 (8.15R15)	7.0-15	706	230	25	10.00	Tube Type	4225	3250
250R15	250/70R15	7.0-15	736	252	27	10.00	Tube Type	4745	3650
300R15	315/70R15	8.0-15	835	312	36	10.00	Tube Type	6695	5150
10.00R20	290/95R20	7.5-20	1062	294	35	10.00	Tube Type	6890	5300
12.00R20	330/95R20	8.5-20	1136	320	41	10.00	Tube Type	9230	7100
12.00R24	330/95R24	8.5-24	1232	322	39	10.00	Tube Type	9750	7500
14.00R24	385/95R24	10.0-24	1416	390	64	10.00	Tube Type	14950	11500
16.00R25*	445/95R25	11.25-25/2.0	1495	424	56	10.00	Tubeless	18200	14000
18.00R25	505/95-25	13.00-25/2.5	1636	478	68	10.00	Tubeless	27560	21200
18.00R33	505/95-33	13.00-33/2.5	1838	486	74	10.00	Tubeless	31590	24300

* Only for use on port applications including straddle carriers and other crane type machinery

TREAD PATTERNS



TR-900

TR-900
16.00R25



TRELLEBORG