



MID-RANGE MATERIALS HANDLING PNEUMATIC

T-800

Balanced Performance

The T-800 pneumatic tire range has been developed to deliver good performance at a competitive price for forklifts and other industrial equipment. The lug tread pattern provides optimal grip and traction. The cross-ply/diagonal structure ensures high stability and comfort.

PERFORMANCE DEFINED

TIRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.

ENERGY SAVING

Trelleborg is a **leading approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

STABILITY

Trelleborg tires are designed with **exceptional stability**. Our tires are engineered to ensure **proper distribution of heat** and to prevent excessive deflection under load.

COMFORT

Trelleborg recognizes the importance of a **safe working environment**. Our products are designed to minimize vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

MID-RANGE MATERIALS HANDLING PNEUMATIC

T-800

Tire Size	Alternative Size	Ply Rating	Rim Size	Tire Dimensions (in)		Tread Depth (32nds)	Inflation Pressure (psi)	Tire Type	Load Capacity (lbs)		Weight (lbs)
				Overall Diameter	Section Width				Forklift trucks up to 15 mph		
									Load Wheel	Steering Wheel	
5.00-8		10	3.00D-8	18.6	5.4	18	145	Tube Type	3,120	2,405	13
18x7-8	180/70-8	16	4.33R-8	18.0	6.4	23	145	Tube Type	4,730	3,640	19
6.00-9		12	4.00E-09	20.8	6.1	20	145	Tube Type	4,155	3,195	22
21x8-9	200/75-9	14	6.00E-09	21.5	8.1	23	131	Tube Type	5,590	4,300	27
6.50-10		10	5.00F-10	23.5	7.1	19	112	Tube Type	4,300	3,305	26
7.50-10		12	5.5-10	25.4	7.7	20	120	Tube Type	5,090	4,300	43
23x9-10	225/75-10	20	6.50F-10	23.1	9.1	23	145	Tube Type	7,595	5,840	49
7.00-12		14	5.00S-12	26.6	7.5	25	131	Tube Type	6,075	4,675	37
27x10-12	250/75-12	14	8.00G-12	27.4	9.7	28	102	Tube Type	7,815	6,010	52
7.00-15	29x8-15	14	5.5-15	32.5	10.0	23	131	Tube Type	7,165	5,510	47
8.25-15		14	6.5-15	32.5	10.0	26	116	Tube Type	9,315	7,165	63
28x9-15	225/75-15 (8.15-15)	14	7.0-15	28.4	8.5	24	145	Tube Type	8,600	6,615	48
250-15	250/70-15	20	7.0-15	30.4	9.8	25	145	Tube Type	11,110	8,545	65
300-15	315/70-15	20	8.0-15	33.7	11.4	30	131	Tube Type	14,330	11,025	105

TREAD PATTERN

T-800



TRELLEBORG.COM/WHEELS