



PREMIUM MATERIALS HANDLING PRESS-ON SOLID

TRELLEBORG

Designed to Perform Made to Excel

Trelleborg Press-On tires are the total solution for all your materials handling equipment needs. They are designed to provide excellent wear and energy efficiency.

Trelleborg Press-On tires are available in traction and smooth profiles:

The **Traction** profile offers long wear and distributes the load for excellent stability.

The **Smooth** profile has an average 13% greater footprint than a standard press-on tire. The larger footprint provides a more comfortable tire and improves performance and traction.



PERFORMANCE DEFINED

TIRE WEAR

Our expertise in design ensures that our tires are **built to last** in demanding environments. Our tires are designed to match the requirements of the global leading OEM producers delivering a wear **performance that exceeds** all others in their class.

TIRE LIFE

Trelleborg products guarantee **the best tire** performance in the industry. This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.

ENDURANCE

Our tires are built to deliver the **best heat resistance performance** in their class. We invest in **compounding technology and quality raw materials** to ensure exceptional heat resistance. Combined, these allow our tires to cope safely with heat build-up longer.

ENERGY SAVING

Trelleborg is a **leading approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

*Testing results concluded from TWS field-testing program.

PREMIUM MATERIALS HANDLING PRESS-ON SOLID

TRELLEBORG**PERFORMANCE AGAINST PREMIUM COMPETITOR**

- 25% Longer Tire Life
- 19% Longer Tire Wear
- 16% More Endurance
- 12% Energy Savings

METRIC SIZES

Tire Size	Pattern & Profile			Load Capacity [kg]				
	Smooth		Traction	Other vehicles up to			Forklift trucks up to 25 km/h	
	Flat	Crown	Flat	6 km/h	10 km/h	16 km/h	Load Wheel	Steering Wheel
125x50x75	FL			160	130	100		
150x50x100	FL			225	180	135		
150x75x100	FL			375	300	230		
160x50x100	FL			250	200	150		
200x75x100	FL			500	400	300		
200x85x105	FL			550	440	330		
200x130x105	FL			880	725	660		
186x70x120	FL			455	370	280		
180x75x120	FL			475	380	290		
200x50x140	FL			350	280	210		
250x75x140	FL			625	500	400		
250x130x140	FL		GS	1065	875	800	775	635
260x75x140	FL			630	510	385		
280x75x140	FL			630	505	385		
254x90x145	FL			670	545	395		
250x90x150	FL			670	545	395		
220x60x160	FL			450	360	270		
265x160x160	FL			1420	1165	1015	1030	845
230x75x170	FL			625	500	380		
250x80x170	FL			675	540	410		
250x90x170	FL			840	670	425		
250x105x170	FL			780	645	700	570	465
260x85x170	FL		GL	775	620	465		
260x105x170	FL		GS	825	675	615		
260x130x170	FL			1065	875	795		
300x85x170	FL			800	640	480		
315x145x180	FL			1480	1215	1055		
330x145x180	FL			1540	1265	1100		
290x105x185	FL		GS	905	745	645		
300x80x185	FL			760	610	455		
250x50x190	FL			450	360	270		
250x85x190	FL			745	595	455		
330x145x194	FL			1535	1260	1095		
300x90x203	FL			900	720	540		
300x100x203	FL		GS	870	715	650	635	520
313x130x203	FL		GS	1260	1035	945		
280x75x220	FL			705	565	425		
285x75x220	FL			725	580	440		
310x60x220	FL			650	520	390		
300x75x225	FL			725	585	445		
300x100x230	FL			1010	815	615		
300x75x240	FL			700	560	420		
305x75x240	FL			700	560	420		

CONTINUED ON NEXT PAGE

PREMIUM MATERIALS HANDLING PRESS-ON SOLID

TRELLEBORG

METRIC SIZES

Tire Size	Pattern & Profile			Load Capacity [kg]				
	Smooth		Traction	Other vehicles up to			Forklift trucks up to 25 km/h	
	Flat	Crown	Flat	6 km/h	10 km/h	16 km/h	Load Wheel	Steering Wheel
360x60x270	FL			750	600	450		
360x75x270	FL			950	760	570		
360x85x270	FL			1050	840	630		
450x120x300	FL			1495	1230	1120		
405x65x305	FL			900	720	540		
405x130x305	FL		GS	1510	1240	1135	1095	900
405x220x305		PL		2760	2265	1970		
405x260x305	FL			3325	2730	2495	2415	1980
415x75x305	FL			1000	800	590		
415x90x305	FL			1060	875	760		
415x100x305	FL			1115	915	835	810	665
425x150x305	FL			1910	1570	1435	1385	1135
425x260x305	FL			3620	2970	2720	2630	2155
450x260x305	FL			3620	2965	2585	2865	2350
450x300x305	FL			4265	3490	3045	3375	2765
440x200x330	FL			2710	2225	2030		
500x85x370	FL			1300	1050	785		
500x100x370	FL			1270	1040	955		
500x140x370	FL			1995	1640	1495		
500x280x370	FL			4535	3725	3405		
520x120x370	FL			1670	1370	1255	1215	995
550x120x410	FL			1750	1440	1315	1270	1040
550x160x410	FL			2550	2100	1915	1855	1520
610x100x410	FL			1265	1040	950		
610x150x410	FL			2505	2055	1880	1815	1490
620x200x410	FL			3790	3110	2840	2745	2250
630x180x410	FL			3300	2710	2475		
645x250x410	FL			4810	3930	3430	3305	2745
645x300x410	FL			6060	4960	4330	4170	3460
645x350x410	FL			7315	5985	5225	5035	4180
670x200x410	FL			3940	3235	2955		
680x150x470	FL			2690	2210	2020		
710x300x470	FL			6525	5340	4660		
645x200x480	FL			3865	3175	2900	2800	2295
660x203x480			GL	3695	3025	2645	2545	2110
660x250x480			GL / GS	4780	3910	3415	3290	2735
705x180x485	FL			3590	2950	2695		
760x250x500	FL			5440	4450	3885	3740	3105
780x200x555	FL			4485	3685	3365	3255	2665
854x320x600	FL			8165	6680	5835		
926x240x670	FL			5970	4885	4265		
968x240x670	FL			6095	4985	4350		

SPECIAL COMPOUNDS AVAILABLE



Non-Marking



Electrically Conductive



Power Saver (Rolling Resistant)



Heavy Duty



Chemical Resistant (Scrubber)

TREAD PATTERNS



FL



GL

Note: In case of multiple tread pattern profiles for the same size, the provided weight refers to FL.

PREMIUM MATERIALS HANDLING PRESS-ON SOLID

TRELLEBORG

IMPERIAL SIZES

Tire Size	Metric Size	Pattern & Profile			Load Capacity [kg]				
		Smooth		Traction	Other vehicles up to			Forklift trucks up to 25 km/h	
		Flat	Crown	Flat	6 km/h	10 km/h	16 km/h	Load Wheel	Steering Wheel
9x5x5	229x127x127	FL			960	790	680	695	570
10x4x6¼	254x102x159	FL			780	640	560	565	465
10x4x6½	254x102x165	FL			780	640	555	565	465
10x5x6½	254x127x165	FL			1010	830	725	735	605
10½x5x6½	267x127x165	FL		GL	1070	880	770	780	640
10½x7x6½	267x178x165	FL			1600	1310	1140	1160	950
13x3½x8	330x89x203			GL	785	645	615	570	470
13x4½x8	330x114x203	FL		GL	1120	920	800	815	670
13x5x8	330x127x203			GL	1290	1060	920	935	765
13½x5½x8	343x140x203	FL		GL	1510	1240	1080	1095	895
14x4½x8	356x114x203	FL		GL	1170	960	830	850	695
14x5x10	356x127x254	FL			1335	1095	955	970	795
15½x5x10	394x127x254	FL		GL	1470	1210	1050	1070	875
16x5x10½	406x127x267	FL		GL	1510	1240	1080	1095	895
16x6x10½	406x152x267	FL		GL	1910	1570	1360	1390	1140
16x7x10½	406x178x267			GL	2325	1910	1660	1685	1380
15x5x11¼	381x127x286	FL		GL	1390	1140	990	1010	830
15x6x11¼	381x152x286	FL		GL	1715	1410	1225	1245	1020
16¼x5x11¼	413x127x286	FL		GL	1530	1250	1090	1105	905
16¼x6x11¼	413x152x286	FL	PL	GL	1920	1580	1370	1395	1140
16¼x7x11¼	413x178x286			GL	2325	1900	1650	1680	1380
17x4½x121/8	432x114x308			GL	1370	1130	980	995	815
17x5x121/8	432x127x308	FL		GL	1570	1290	1120	1145	935
17x6x121/8	432x152x308			GL	1980	1630	1410	1435	1180
18x5x121/8	457x127x308	FL		GL	1640	1350	1170	1195	980
18x6x121/8	457x152x308	FL		GL	2100	1720	1500	1525	1250
18x7x121/8	457x178x308	FL		GL	2550	2100	1820	1855	1520
18x8x121/8	457x203x308	FL		GL	3000	2475	2150	2180	1790
18x9x121/8	457x229x308	FL		GL	3450	2850	2475	2510	2060
21x6x15	533x152x381	FL		GL	2350	1930	1680	1710	1400
21x7x15	533x178x381	FL	PL	GL	2875	2350	2050	2085	1710
21x8x15	533x203x381	FL		GL	3375	2775	2425	2455	2015
21x9x15	533x229x381	FL		GL	3900	3200	2775	2830	2320
22x7x16	559x178x406	FL		GL	2975	2450	2125	2160	1770
22x8x16	559x203x406	FL	PL	GL	3500	2875	2500	2545	2085
22x9x16	559x229x406	FL		GL	4050	3325	2875	2930	2400
22x10x16	559x254x406	FL		GL	4575	3750	3250	3315	2720
22x12x16	559x305x406	FL		GL	5625	4625	4025	4090	3350
22x14x16	559x356x406	FL			6700	5505	4785	4865	3990
22x16x16	559x406x406	FL			7745	6360	5530	5625	4610
22x6x17¼	559x152x451	FL			2345	1925	1675	1700	1395

PREMIUM MATERIALS HANDLING PRESS-ON SOLID

TRELLEBORG


IMPERIAL SIZES

Tire Size	Metric Size	Pattern & Profile			Load Capacity [kg]				
		Smooth		Traction	Other vehicles up to			Forklift trucks up to 25 km/h	
		Flat	Crown	Flat	6 km/h	10 km/h	16 km/h	Load Wheel	Steering Wheel
26x7x20	660x178x508	FL			3375	2775	2400	2445	2005
28x10x22	711x254x559	FL			5470	4490	3905	3970	3255
28x12x22	711x305x559	FL		GL	6740	5540	4820	4900	4015
28x14x22	711x356x559	FL			8020	6590	5720	5820	4780
28x16x22	711x406x559	FL			9270	7620	6620	6730	5520
40x12x30	1016x305x762	FL			8760	7170	5690	6030	5010
40x14x30	1016x356x762	FL			10610	8675	6890	7300	6060
40x16x30	1016x406x762	FL			12420	10160	8060	8550	7095
40x20x30	1016x508x762	FL			16120	13180	10460	11090	9210

SPECIAL COMPOUNDS AVAILABLE

				
Non-Marking	Electrically Conductive	Power Saver (Rolling Resistant)	Heavy Duty	Chemical Resistant (Scrubber)

TREAD PATTERNS



Note: In case of multiple tread pattern profiles for the same size, the provided weight refers to FL.



Trelleborg is a world leader in engineered polymer solutions that seal, damp and protect critical applications in demanding environments. Our innovative engineered solutions accelerate performance for customers in a sustainable way. The Trelleborg Group has local presence in over 40 countries around the world.