



ECONOMY MATERIALS HANDLING RESILIENT

## **ECOSOLID**

### **Pneumatic Shaped Solid**

Ecosolid is an entry-level solid tire option available in the 8" to 15" size range.

Ecosolid is designed for use on forklifts in light-duty application.

#### **FEATURES**

- Available in standard black compounds
- Steel-reinforced base
- Wear indicator built in to lug design

\*Testing results concluded from TWS field-testing program.

## ECONOMY MATERIALS HANDLING RESILIENT ECOSOLID

Tire Size	Alternative Size	Rim Size	LOC	Tire Dimensions [mm]		Load Capacity [kg]		
				Overall Diameter	Section Width	Static	Forklift trucks up to 25 km/h	
							Load Wheel	Steering Wheel
<b>15x4½-8</b>	125/75-8	3.00D-8	•	372	103	1210	1040	800
<b>5.00-8</b>		3.00D-8	•	457	122	1650	1415	1090
<b>16x6-8</b>	150/75-8	4.33R-8	•	408	143	1740	1495	1150
<b>18x7-8</b>	180/70-8	4.33R-8	•	450	143	2490	2145	1650
<b>140/55-9</b>	15x5.5-9	4.00E-09	•	370	127	1360	1170	900
<b>6.00-9</b>		4.00E-09	•	508	140	2190	1885	1450
<b>21x8-9</b>	200/75-9	6.00E-09	•	508	185	3200	2755	2120
<b>6.50-10</b>		5.00F-10	•	559	163	2720	2340	1800
<b>200/50-10</b>		6.50F-10	•	447	186	2870	2470	1900
<b>23x9-10</b>	225/75-10	6.50F-10	•	571	190	4000	3445	2650
<b>7.00-12</b>		5.00S-12	•	660	168	3380	2920	2240
<b>23x10-12</b>	250/60-12	8.00G-12	•	571	224	4380	3770	2900
<b>27x10-12</b>	250/75-12	8.00G-12	•	656	230	4530	3900	3000
<b>8.25-15</b>		6.5-15	•	787	206	5510	4750	3650
<b>28x9-15</b>	225/75-15 (8.15-15)	7.0-15	•	686	204	4000	3445	2650
<b>250-15</b>	250/70-15	7.0-15	•	711	216	5510	4745	3650
<b>300-15</b>	315/70-15	8.0-15	•	812	254	6795	5850	4500
<b>355/65-15</b>	32x12½-15 (350-15)	9.75-15	•	809	279	9060	7800	6000

### AVAILABLE COMPOUNDS



Standard  
Black

### TREAD PATTERNS



Ecosolid



TRELLEBORG

WWW.TRELLEBORG.COM/WHEELS