



MID-RANGE MATERIALS HANDLING RESILIENT

ORCA

Balanced Performance

Orca is designed with one objective: performance at a competitive price. For applications that are not in constant use or that carry a lower load, as standard Orca proves itself as the most cost-effective tire in its class. Long mileage, low energy consumption and excellent cut resistance all mean that Orca delivers a solid performance at the right price.

Orca tires are available in the most common sizes in both LOC and NON LOC (nose retaining bead for easy mounting).

PERFORMANCE DEFINED

TIRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.

ENERGY SAVING

Trelleborg is a **leading approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

STABILITY

Trelleborg products are designed to have **large footprints** maximizing the contact area leading to better stability and even tire wear.

COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

MID-RANGE MATERIALS HANDLING RESILIENT

ORCA

Tire Size	Alternative Size	Rim Size	LOC	Tire Dimensions [mm]		Load Capacity [kg]		
				Overall Diameter	Section Width	Static	Forklift trucks up to 25 km/h	
							Load Wheel	Steering Wheel
4.00-8		3.00D-8	•	398	94	1100	950	730
15x4½-8	125/75-8	3.00D-8	•	373	110	1210	1040	800
5.00-8		3.00D-8	•	452	114	1650	1415	1090
16x6-8	150/75-8	4.33R-8	•	409	143	1740	1495	1150
18x7-8	180/70-8	4.33R-8	•	445	147	2490	2145	1650
140/55-9	15x5.5-9	4.00E-09	•	380	132	1360	1170	900
6.00-9		4.00E-09	•	520	130	2190	1885	1450
21x8-9	200/75-9	6.00E-09	•	514	180	3200	2755	2120
6.50-10		5.00F-10	•	568	153	2720	2340	1800
200/50-10		6.50F-10	•	450	175	2870	2470	1900
23x9-10	225/75-10	6.50F-10	•	574	187	4000	3445	2650
7.00-12		5.00S-12	•	646	163	3380	2920	2240
23x10-12	250/60-12	8.00G-12	•	570	219	4380	3770	2900
27x10-12	250/75-12	8.00G-12	•	670	235	4530	3900	3000
7.00-15	29x8-15	5.5-15	•	717	162	4115	3545	2725
7.50-15		6.5-15	•	743	186	4530	3900	3000
8.25-15		6.5-15	•	803	192	5510	4750	3650
28x9-15	225/75-15 (8.15-15)	7.0-15	•	680	200	4530	3900	3000
250-15	250/70-15	7.0-15	•	709	206	5510	4750	3650
250-15	250/70-15	7.5-15	•	709	206	5510	4750	3650
300-15	315/70-15	8.0-15	•	807	244	6795	5850	4500
355/65-15	32x12½-15 (350-15)	9.75-15	•	809	260	9060	7800	6000

SPECIAL COMPOUNDS AVAILABLE

Non-Marking

TREAD PATTERNS

Orca



WWW.TRELLEBORG.COM/WHEELS