



Binnenbanden STT PLUS



	BANDENMAAT	TYPE VENTIEL
Ø24		
	11.2-24	TR218A
	12.4-24	TR218A
	13.6-24	TR218A
	14.9-24	TR218A
Ø26		
	14.9-26	TR218A
	16.9-26	TR218A
	18.4-26	TR218A
	28L26	TR218A
Ø28		
	11.2-28	TR218A
	12.4-28	TR218A
	13.6-28	TR218A
	14.9-28	TR218A
	16.9-28	TR218A
	18.4-28	TR218A
Ø30		
	14.9-30	TR218A
	16.9-30	TR218A
	18.4-30	TR218A
	23.1-30	TR218A
Ø32		
	8.3-32	TR218A
	9.5-32	TR218A
	11.2-32	TR218A
	12.4-32	TR218A
	24.5-32	TR218A
	30.5-32	TR218A
Ø34		
	16.9-34	TR218A
	18.4-34	TR218A
	20.8-34	TR218A
	23.1-34	TR218A
Ø36		
	8.3-36	TR218A
	9.5-36	TR218A
	11.2-36	TR218A
	12.4-36	TR218A
	13.6-36	TR218A

BANDENMAAT	TYPE VENTIEL
Ø38	
11.2-38	TR218A
12.4-38	TR218A
13.6-38	TR218A
14.9-38/15.5-38	TR218A
16.9-38	TR218A
18.4-38	TR218A
20.8-38	TR218A
Ø42	
9.5-42	TR218A
11.2-42	TR218A
18.4-42	TR218A
20.8-42	TR218A
Ø44	
11.2-44	TR218A
Ø46	
12.4-46	TR218A
Ø48	
9.5-48/230/95-48	TR218A
11.2-48/270/95-48	TR218A