

Binnenbanden STT TWIN Aanhangwagens & Industriële Trekkers



	BANDENMAAT	TYPE VENTIEL
Ø4		
	200x50	TR87
	2.50-3/2.50-4	TR87
	3.00-4,260X85	TR87
	4.00-4,4.10-4,4.10/3.50-4	TR87
Ø5		
	11X4.00-5	TR87
Ø6		
	4.10/3.50-6, 4.00-6, 13X5.00-6	TR13
	4.10/3.50-6, 4.00-6, 13X5.00-6	TR87
	140-6	TR87
	15X6.00-6	TR13
	220/50-6	TR13
Ø8		
	3.00-8	TR13
	3.50/4.00/4.80-8, 400X100	TR13
	3.50/4.00/4.80-8, 400X100	TR87
	4.00-8 BV 202	TR13
	16x6.50-8/190-8	TR13
	16x8.50/9.50-8	TR13
	5.00-8	TR13
	5.00-8	TR87
	5.00-8	JS2
	18x7-8	JS2
	18X7.00/7.50/8.50/8.5/9.50-8	TR13
	20X10.00-8	TR13
Ø9		
	6.00-9	TR15
	6.00-9	TR87
	6.00-9	V3-02-19 (TR274)
	6.00-9	JS2
	21X8-9	JS2
Ø10		
	3.50-10	TR87
	4.00/4.10-10, 4.40-10, 5.00-10	TR13
	6.50-10	JS2
	6.50-10	TR75
	7.50-10	TR135
	7.50-10	TR150
	7.50-10	JS2
	9.00/9.50-10	TR135
	20X8.00-10	TR13
	20.5X10.00-10	TR13
	23X9-10	JS2
Ø12		
	4.00-12	TR13
	6-12	TR13
	7.00-12	TR15
	7.00-12	TR75
	23x10-12	TR75
	27x10-12	JS2
	560X140-12	TR13
	8.50-12/10.0/80-12	TR15
	23x8.50/10.50-12	TR13
	26x12.00-12	TR13

BANDENMAAT	TYPE VENTIEL
Ø13	
5.00-13/23x5	V3-02-8 (TR76)
610X145-13	TR13
9.00-13	TR15
Ø14	
645X160-14	TR13
Ø14.5	
200/60-14.5	TR15
Ø15	
27X8.50-15	TR15
300-15	TR77
4.00-15/125-15	TR13
5.00-15	TR13
165-15	TR13
28x12.5-15	TR75A
7.5L15	TR218
7.00-15/250-15	V3-02-8 (TR76)
7.50-15	V3-02-8 (TR76)
27x8.50-15	TR15
8.15-15 (28x9-15)	V3-02-27 (TR75)
215/65-15	TR15
8.25-15	V3-02-26 (TR77)
10.00-15	TR75
29X12.50-15	TR15
Ø15.3	
10.0/75-15.3	TR15
11.5/80-15.3	TR15
11.5/80-15.3	TR218
12.5/80-15.3	TR15
10.5/11.5/12.5/80-15.3	TR15
Ø16	
4.00/4.50-16	TR15
5.00/5.50-16	TR15
6.00-16	TR15
6.50/7.00-16	TR15
7.50-16	TR15
9.00-16	TR15
10.00-16	TR15
10.00-16	TR218
10.5/65-16	TR15
11.00-16	TR15
13.0/55-16	TR15
14.0/65-16/13.0/75-16	TR15
Ø16.5	
10-16.5	TR15
12-16.5	TR15
Ø17	
15.0/55-17	TR15
19.0/45-17/500/50-17	TR15

BANDENMAAT	TYPE VENTIEL
Ø18	
7.50-18	TR15
10.5/80-18	TR15
12.5/80-18/13.0/65-18	TR218
12.5/80-18/13.0/65-18	TR15
15.0/70-18	TR15
Ø19	
4.00-19	TR15
6.00-19	TR15
Ø20	
6.50/7.00-20	V3-02-27 (TR75)
7.50-20	V3-02-8 (TR76)
7.50-20	TR15
8.25-20	V3-02-26 (TR77)
10.5/80-20	TR15
12.5/80-20	TR15
14.5/80-20	TR15
16.0/70-20	TR15