

Binnenbanden STT TWIN Bosbouwbanden



BANDENMAAT		TYPE VENTIEL
Ø22.5		
	600/50-22.5/650/45-22.5	TR218
	710/40-22.5	TR218
Ø24.5		
	710/45-24.5	TR218
Ø26.5		
	600/55-26.5/650/60-26.5	TR218
	710/45-26.5/750/50-26.5	TR218
Ø30.5		
	710/50-30.5/750/45-30.5	TR218
Ø34		
	600/65-34/710/55-34	TR218