

# Cámaras STT para Tractor



	MEDIDA	MODELO VALVULA
<b>Ø20</b>		
	9.5-20	TR218
	11.2-20	TR218
<b>Ø24</b>		
	8.3-24	TR218
	9.5-24	TR218
	320/70-24/11.2-24	TR218
	360/70-24/12.4-24	TR218
	380/70-24/13.6-24	TR218
	420/70-24/14.9-24	TR218
	16.9-24/16.5/85-24	TR218
<b>Ø26</b>		
	14.9-26	TR218
	16.9-26	TR218
	18.4-26	TR218
	23.1-26	TR218
	28L-26	TR218
<b>Ø28</b>		
	8.3-28	TR218
	9.5-28	TR218
	320/70-28/11.2-28	TR218
	360/70-28/12.4-28	TR218
	380/70-28/13.6-28	TR218
	420/70-28/14.9-28	TR218
	480/70-28/16.9-28	TR218
	18.4-28	TR218
<b>Ø30</b>		
	420/70-30/14.9-30	TR218
	480/70-30/16.9-30	TR218
	520/70-30/18.4-30	TR218
	23.1-30	TR218
<b>Ø32</b>		
	8.3-32	TR218
	9.5-32	TR218
	11.2-32	TR218
	12.4-32	TR218
	24.5-32	TR218
	30.5-32	TR218
<b>Ø34</b>		
	16.9-34	TR218
	18.4-34	TR218
	20.8-34	TR218
	23.1-34	TR218
<b>Ø36</b>		
	7.2-36	TR218
	8.3-36	TR218
	9.5-36	TR218
	11.2-36	TR218
	12.4-36	TR218
	13.6-36	TR218

MEDIDA	MODELO VALVULA
<b>Ø38</b>	
8.3/9.5-38	TR218
11.2-38	TR218
12.4-38	TR218
13.6-38	TR218
14.9-38/15.5-38	TR218
16.9-38	TR218
18.4-38	TR218
20.8-38	TR218
<b>Ø40</b>	
9.5-40/230/95-40	TR218
<b>Ø42</b>	
8.3-42	TR218
9.5-42	TR218
11.2-42	TR218
18.4-42	TR218
18.4R20.8R42	TR218A
20.8-42	TR218
<b>Ø44</b>	
8.3/9.5-44/210/230/95-44	TR218
11.2-44	TR218
<b>Ø46</b>	
12.4-46	TR218
18.4R46	TR218A
14.9-46	TR218
20.8R46	TR218A
<b>Ø48</b>	
9.5-48/230/95-48	TR218
11.2-48/270/95-48	TR218
13.6-48	TR218
<b>Ø50</b>	
16.9R50	TR218
18.4R50	TR218