



PREMIUM CONSTRUCTION SOLID

## BRAWLER™ HD SKID STEER

Brawler™ Skid Steer tires are designed to eliminate downtime and provide superior vehicle performance in severe-duty applications. They feature an enhanced rubber compound designed for greater resistance to cutting and chunking. Trelleborg manufactures Solidflex tires that feature elliptical apertures and HD tires that are aperture free.

Installation of the HD Skid Steer is simple. No pressing is required — the tire features a built-in wheel that simply bolts on. The Brawler™ Skid Steer is constructed using a premium mining rubber compound that is abrasion and chunk resistant. The Brawler™ Solidflex is also available in a Non-Marking compound.



HD Solidflex  
Traction

HD Solidflex  
Smooth

HD  
Traction

HD  
Smooth

### FEATURES AND BENEFITS

- Durable cut-resistant rubber compound eliminates downtime caused by flats and sidewall cuts
- No specialized equipment required to install
- Passed the rigorous testing of OEMs.

### APPLICATIONS

- Skid Steer
- Backhoes
- Mining
- Aerial Boom
- Trencher
- Compact Tractor

PREMIUM CONSTRUCTION SOLID  
**BRAWLER™ HD**  
**SKID STEER**

#### HD SOLIDFLEX TRACTION

Tire Size	Pneumatic Equivalent Size	Overall Diameter (in)	Section Width (in)	Rubber Thickness (in)	Tread Depth (32nds)	Load Capacity 6 mph (lbs)	Weight (lbs)
<b>31x6x10</b>	10-16.5	30.9	10.0	6.2	60	6,615	230
<b>33x6x11</b>	12-16.5	33.1	11.0	6.1	77	7,935	281
<b>36x7x11</b>	14-17.5	36.0	11.0	6.6	89	8,565	342

#### HD SOLIDFLEX SMOOTH

Tire Size	Pneumatic Equivalent Size	Overall Diameter (in)	Section Width (in)	Rubber Thickness (in)	Tread Depth (32nds)	Load Capacity 6 mph (lbs)	Weight (lbs)
<b>31x5x9</b>	10-16.5	31.0	9.0	5.1	60	5,910	253
<b>33x6x8</b>	8.00-16	33.1	8.0	6.1	77	5,510	257
<b>33x6x10</b>	12-16.5	33.1	10.0	6.1	77	7,365	290



PREMIUM CONSTRUCTION SOLID  
**BRAWLER™ HD**  
**SKID STEER**

### HD TRACTION

Tire Size	Pneumatic Equivalent Size	Overall Diameter (in)	Section Width (in)	Rubber Thickness (in)	Tread Depth (32nds)	Load Capacity 6 mph (lbs)	Weight (lbs)
<b>31x5x7</b>	7.50-16	31.0	7.0	5.2	48	5,410	190
<b>31x5x9</b>	10-16.5	31.0	9.0	5.2	48	7,230	245
<b>33x6x8</b>	8.00-16	33.1	8.0	6.1	58	6,340	257
<b>33x6x10</b>	12-16.5	33.1	10.0	6.1	58	8,170	311

### HD SMOOTH

Tire Size	Pneumatic Equivalent Size	Overall Diameter (in)	Section Width (in)	Rubber Thickness (in)	Tread Depth (32nds)	Load Capacity 6 mph (lbs)	Weight (lbs)
<b>31x5x7</b>	7.50-16	31.0	7.0	5.2	60	5,410	196
<b>31x5x9</b>	10-16.5	31.0	9.0	5.2	60	7,230	265
<b>33x6x8</b>	8.00-16	33.1	8.0	6.1	77	6,340	263
<b>33x6x10</b>	12-16.5	33.1	10.0	6.1	77	8,170	320
<b>36x7x11</b>	14-17.5	36.0	11.0	6.7	89	9,330	420

**Note: Tread depth on smooth tires indicates wearable rubber.**





Trelleborg is a world leader in engineered polymer solutions that seal, damp and protect critical applications in demanding environments. Our innovative engineered solutions accelerate performance for customers in a sustainable way. The Trelleborg Group has local presence in over 40 countries around the world.

[WWW.TRELLEBORG.COM/WHEELS](http://WWW.TRELLEBORG.COM/WHEELS)