



# Twin Tractor. Benefits at first sight



  
Download the App for free



Tire iBrochure

# Twin Tractor

**A traction pattern with deep lugs in three different angles for maximum traction and excellent self cleaning.**

Extra large contact area with full width load distribution and greatly reduced soil compaction  
Twin Tractor tires can easily replace dual wheel fitments

Low wheelslip promotes maximum horsepower utilization and efficiency with minimum fuel consumption

Excellent ground stability and improved driver comfort thanks to the diagonal belt design which combines the best of both radial and cross-ply construction



SIZE	LI/SS	Tread Pattern	New tire		Tire in service		SLR inches	RC inches	SRI inches	Rim	Type
			SW inches	OD inches	SW inches	OD inches					
<b>400/55-17.5</b>	125A8 (122B)	<b>T414</b>	15.7	34.6	17	35.7	16.1	103.9	415	AG11.75	TUBELESS
<b>600/55-26.5</b>	148A8 (145B)	<b>T414</b>	23.6	53.1	25.5	54.3	24.4	159.4	625	AG20.00	TUBELESS
<b>600/55-30.5</b>	150A8 (147B)	<b>T414</b>	23.6	56.5	25.5	58.1	26.4	170.5	675	AG20.00	TUBELESS
<b>600/60-30.5</b>	153A8 (150B)	<b>T414</b>	23.6	59.4	25.1	60.8	27.6	176.6	700	AG20.00	TUBELESS
<b>800/55-30.5</b>	172A8 (168B)	<b>T414</b>	32.3	65	33.9	67.6	29.9	192.9	770	AG28.00	TUBELESS
<b>900/60-32</b>	176A8 (173B)	<b>T414</b>	35.4	74.4	38.6	77.5	33.9	222	880	DW27B	TUBELESS
<b>710/65-38</b>	162A8 (158B)	<b>T414</b>	28	73.2	30.5	76.9	34.3	221.5	885	DW24B	TUBELESS
<b>850/50-38</b>	163A8 (160B)	<b>T414</b>	33.5	73.2	36.3	73.8	33.5	219.7	855	DW28B	TUBELESS
<b>850/60-38</b>	175A8 (172B)	<b>T414</b>	33.5	78	36.3	81	35.8	231.5	930	DW28B	TUBELESS
<b>850/55-42</b>	161A8 (157B)	<b>T414</b>	33.5	78.3	36.3	81.4	35.4	231.5	945	DW28B	TUBELESS



Trelleborg Wheel Systems Americas, Inc  
570 Trelleborg Drive, Spartanburg, SC 29301  
Toll Free Phone Number: 1-866-633-8473  
[www.trelleborg.com/wheels/us](http://www.trelleborg.com/wheels/us)

