



MID-RANGE MATERIALS HANDLING RESILIENT

ORCA

Balanced Performance

Orca is designed with one objective: performance at a competitive price. For applications that are not in constant use or that carry a lower load, as standard Orca proves itself as the most cost-effective tire in its class. Long mileage, low energy consumption and excellent cut resistance all mean that Orca delivers a solid performance at the right price.

Orca tires are available in the most common sizes in both LOC and NON LOC (nose retaining bead for easy mounting).

PERFORMANCE DEFINED

TIRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.

ENERGY SAVING

Trelleborg is a **leading approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

STABILITY

Trelleborg products are designed to have **large footprints** maximizing the contact area leading to better stability and even tire wear.

COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

MID-RANGE MATERIALS HANDLING RESILIENT

ORCA

Tire Size	Alternative Size	Rim Size	LOC	Tire Dimensions (in)		Load Capacity (lbs)			Weight (lbs)
				Overall Diameter	Section Width	Static	Forklift Trucks up to 15 mph		
							Load Wheel	Steering Wheel	
4.00-8		3.00D-8	•	15.7	3.7	2,425	2,095	1,610	21
15x4½-8	125/75-8	3.00D-8	•	14.7	4.3	2,670	2,295	1,765	20
5.00-8		3.00D-8	•	17.8	4.5	3,640	3,120	2,405	33
16x6-8	150/75-8	4.33R-8	•	16.1	5.6	3,835	3,295	2,535	33
18x7-8	180/70-8	4.33R-8	•	17.5	5.8	5,490	4,730	3,640	42
140/55-9	15x5.5-9	4.00E-09	•	15.0	5.2	3,000	2,580	1,985	22
6.00-9		4.00E-09	•	20.5	5.1	4,830	4,155	3,195	52
21x8-9	200/75-9	6.00E-09	•	20.2	7.1	7,055	6,075	4,675	70
6.50-10		5.00F-10	•	22.4	6.0	5,995	5,160	3,970	73
200/50-10		6.50F-10	•	17.7	6.9	6,325	5,445	4,190	48
23x9-10	225/75-10	6.50F-10	•	22.6	7.4	8,820	7,595	5,840	92
7.00-12		5.00S-12	•	25.4	6.4	7,450	6,435	4,940	97
23x10-12	250/60-12	8.00G-12	•	22.4	8.6	9,655	8,310	6,395	103
27x10-12	250/75-12	8.00G-12	•	26.4	9.3	9,985	8,600	6,615	152
7.00-15	29x8-15	5.5-15	•	28.2	6.4	9,070	7,815	6,010	117
7.50-15		6.5-15	•	29.3	7.3	9,985	8,600	6,615	142
8.25-15		6.5-15	•	31.6	7.6	12,145	10,470	8,045	178
28x9-15	225/75-15 (8.15-15)	7.0-15	•	26.8	7.9	9,985	8,600	6,615	120
250-15	250/70-15	7.0-15	•	27.9	8.1	12,145	10,470	8,045	139
250-15	250/70-15	7.5-15	•	27.9	8.1	12,145	10,470	8,045	156
300-15	315/70-15	8.0-15	•	31.8	9.6	14,980	12,895	9,920	218
355/65-15	32x12½-15 (350-15)	9.75-15	•	31.9	10.2	19,975	17,195	13,230	252

SPECIAL COMPOUNDS AVAILABLE



Non-Marking

TREAD PATTERNS



Orca



TRELLEBORG.COM/WHEELS