



MID-RANGE MATERIALS HANDLING RESILIENT

## ST-3000

**Deep lug, 3-stage tire available in popular sizes**

Features & Benefits:

- Offers maximum stability under high loads
- Maintains low heat build-up
- Provides optimum resilience for enhanced driver comfort
- Offers maximum abrasion resistance in tough conditions
- Reduces downtime through optimized cost per hour ratios
- Also available in “Talon” (LOC) and Non-Marking White





MID-RANGE MATERIALS HANDLING RESILIENT

**ST-3000**

Tire Size	Rim	LOC	Tread Pattern	Load Capacity (lbs.) Fork lifts, max 16 mph		Other Vehicles (lbs.)			Nominal Sizing (in.)		Weight (lbs)
				Load	Steer	4 mph	6 mph	16 mph	Width	OD	
<b>5.00-8</b>	3.00D-08	Y	ST3	3120	2403	3120	2833	2403	4.9	17.6	34
<b>18x7-8 (180/70-8)</b>	4.33R-8	Y	ST3	4729	3638	4729	4288	3638	5.7	17.8	43
<b>16x6-8 (150/75-8)</b>	4.33R-8	Y	ST3	3208	2469	3208	2910	2469	5.5	16	32
<b>15x4.5-8 (125/75-8)</b>	3.00D-8	Y	ST3	2293	1764	2293	2083	1764	4.4	14.7	20
<b>140/55-9</b>	4.00E-9	Y	ST3	2579	1984	2579	2337	1984	5.1	14.9	23
<b>23x9-10 (225/75-10)</b>	6.50F-10	Y	ST3	7595	5842	7595	6889	5842	7.8	22.2	94
<b>23x10-12 (250/60-12)</b>	R8.00S-12	Y	ST3	8311	6393	8311	7540	6393	9.6	22.6	107
<b>21x8-9</b>	6.00E-9	Y	ST3	6074	4674	6074	5512	4674	7.5	20.6	76
<b>200/50-10</b>	6.50F-10	Y	ST3	5445	4189	5445	4938	4189	7.6	17.7	50
<b>27x10-12</b>	8.00-S12	Y	ST3	8598	6614	8598	7804	6614	9.7	26	153
<b>6.00-9</b>	4.00E-9	Y	ST3	4156	3197	4156	3770	3197	5.4	20.7	55
<b>6.50-10</b>	5.00F-10	Y	ST3	5159	3968	5159	4685	3968	6	22.4	71
<b>7.00-12</b>	5.00S-12	Y	ST3	6415	4938	6415	5831	4938	6.7	25.9	100
<b>28x9-15</b>	7.0-15	Y	ST3	8311	6393	8311	7540	6393	8.1	27.1	123
<b>7.00-15</b>	5.5-15	Y	ST3	7815	6008	7815	7088	6008	6.6	28.1	113
<b>8.25-15</b>	6.5-15	Y	ST3	10461	8047	10461	9491	8047	8.2	31.7	185
<b>250-15 (250/70-15)</b>	7.5-15/7.0-15	Y	ST3	10461	8047	10461	9491	8047	8.3	27.9	138
<b>300-15</b>	8.0-15	Y	ST3	12897	9921	12897	11707	9921	9.9	31.9	227
<b>10.00-20</b>	8.0-20	N	ST/LUG	13228	11023	13228	12015	11023	9.8	40.1	343
<b>12.00-20</b>	8.5-20	N	ST/LUG	16535	13779	16535	15024	13779	10.8	42.4	431
<b>12.00-20</b>	8.0-20	N	ST/LUG	16535	13779	16535	15024	13779	10.8	42.4	426

Available in non-marking in sizes 8-15".

**SPECIAL COMPOUNDS AVAILABLE**

NM

Non-Marking

**TREAD PATTERNS**

ST3

