



Marshland.
The solution for waterlogged
and marshy terrain.



Marshland

Specialized line for use on waterlogged and marshy terrain.

The extremely deep lugs, together with the structure of the carcass, provide high traction and floatation.

SIZE	Tread Pattern	SW mm	OD mm	SLR mm	RC mm	SRI	Rim	Permitted Rims	Type	Tube	
340/85R38 139A8 (139B)	MARSHLAND	405	1660	760	4970	775	W13	W11-W12-DW11DW12-DW13	TUBELESS	16.9-38 TR218	
PRESSURE											
psi	12		14		17		20		23	26	29
bar	0,8		1,0		1,2		1,4		1,6	1,8	2,0
MAX. LOAD kg											
50 S	1560		1775		1995		2215		2430		
40 S	1560		1775		1995		2215		2430		
30 S	1665		1900		2135		2370		2605		
10 LT S	2120		2415		2710		3010		3305	3475	3645
10 HT S	1665		1900		2135		2370		2605		

SIZE	Tread Pattern	SW mm	OD mm	SLR mm	RC mm	SRI	Rim	Permitted Rims	Type	Tube	
420/85R38 144A8 (144B)	MARSHLAND	460	1745	795	5220	800	W15L	W14L-DW14L-DW15L	TUBELESS	16.9-38 TR218	
PRESSURE											
psi	12		14		17		20		23	26	29
bar	0,8		1,0		1,2		1,4		1,6	1,8	2,0
MAX. LOAD kg											
50 S	1795		2045		2300		2550		2800		
40 S	1795		2045		2300		2550		2800		
30 S	1920		2190		2460		2730		3000		
10 LT S	2440		2780		3125		3470		3810	4005	4200
10 HT S	1920		2190		2460		2730		3000		

SIZE	Tread Pattern	SW mm	OD mm	SLR mm	RC mm	SRI	Rim	Permitted Rims	Type	Tube	
460/85R38 149A8 (149B)	MARSHLAND	499	1810	815	5420	825	W16L	W15L-DW15L-DW16L	TUBELESS	18.4-38 TR218	
PRESSURE											
psi	12		14		17		20		23	26	29
bar	0,8		1,0		1,2		1,4		1,6	1,8	2,0
MAX. LOAD kg											
50 S	2080		2375		2665		2960		3250		
40 S	2080		2375		2665		2960		3250		
30 S	2230		2540		2855		3165		3480		
10 LT S	2830		3230		3625		4025		4420	4650	4875
10 HT S	2230		2540		2855		3165		3480		



TRELLEBORG



Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheelsystems