

EMR 1025. High grip, total control.

Protecting people protecting assets

Trelleborg's EMR 1025 winter tire adds extra comfort and safety to snow plowing applications. With its siped winter tread pattern and state-of-the-art compound, EMR 1025 delivers higher grip and traction on snow and reduced

braking distance, so operators and machines get the best possible protection. EMR 1025 offers both the comfort and robustness of the EMR range and the grip of a commercial winter tire.

| Performance | Regulation |
|------------------|------------------------|
| Braking | OCSE code 2 (ISO 6292) |
| Dynamic Traction | OCSE code 2 adp |
| Static Traction | OCSE code 2 adp |

Traction test* (OCSE CODE2_ADP)



Brake test* (ISO 6292:2009)



■ Trelleborg EMR 1025 ■ Competitor A ■ Competitor B

*Test performed by **LPG**
LAPLAND PROVING GROUND

EMR 1025 winter tire



RADIAL CONSTRUCTION



REINFORCED CARCASS



HIGH GRIP ON SNOW



EXCELLENT RIDE COMFORT

Why choose EMR series?



MAXIMUM VALUE
Reduced operating cost per hour



MAXIMUM UPTIME
Increased productivity, higher traction



INCREASED SAFETY
Reduced uncontrolled braking



REDUCED IMPACT
Protecting people, protecting assets

EMR 1025

PREMIUM CONSTRUCTION PNEUMATIC



EMR 1025

| Tire Size | Tread pattern Type | Rim Size (Permitted) | Tread depth (mm) | Service description LI/SS | Tire load capacity (kg) at 40 (km/h) | Tire pressure (bar) | Tire load capacity (kg) at 10 (km/h) | Tire pressure (bar) |
|-------------------|--------------------|---|------------------|---------------------------|--------------------------------------|---------------------|--------------------------------------|---------------------|
| 14.00 R 24 | EMR 1025 TL | 8.00TG-24 SDC (10.00VA-24 SDC) | 24 | * 153 A8 | 3,650 | 3.75 | - | - |
| 17.5 R 25 | EMR 1025 TL | 14.00/1.5-25 (14.00/1.5x25 DC 14.00/1.3x25 DC), | 24 | * 153 A8/176A2 | 3,650 | 3.00 | 7,100 | 4.5 |

*/** – Index of tire strength



Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels