

Trelleborg
Agriculture

Trelleborg tire range



Tractor, combine and sprayer tires

Radial range



TM1000

ProgressiveTraction®



The innovative TM1000 ProgressiveTraction®, designed in compliance with VF regulations, provides superior load capacity, limited soil compaction while providing unbeatable traction. On the road, the new range guarantees low fuel consumption and emissions, long life, boosting farming efficiency.

VF 540/65R30 TL	158D	(155E)	NEW
VF 600/70R30 TL	170D	(167E)	
VF 620/75R30 TL	172D	(169E)	NEW
VF 420/85R34 TL	154D		
VF 650/60R34 TL	168D	(165E)	
VF 710/60R34 TL	173D	(170E)	NEW
VF 650/65R34 TL	170D	(167E)	NEW
VF 650/65R38 TL	172D	(169E)	NEW
VF 650/85R38 TL	182D	(179E)	NEW
VF 710/60R38 TL	174D	(171E)	
VF 800/70R38 TL	184D		
VF 650/65R42 TL	174D	(171E)	NEW
VF 650/75R42 TL	180D	(177E)	NEW
VF 650/85R42 TL	183D	(180E)	NEW
VF 710/70R42 TL	182D	(179E)	NEW
VF 710/75R42 TL	184D	(181E)	NEW
VF 900/60R42 TL	189D	(186E)	NEW
VF 380/85R46 TL	162D	(159E)	NEW
VF 750/75R46 TL	189D	(186E)	NEW
VF 900/65R46 TL	193D	(190E)	
VF 480/80R50 TL	166D		
VF 480/95R54 TL	180D	(177E)	NEW

TM1060



The TM1060 tread design merges the best qualities of Trelleborg's agricultural radial products. Whilst the wing effect maximises the tread width, ensuring an extra wide footprint, the ProgressiveTraction® technology boosts the traction capability. Furthermore, the increased sidewall flexibility leads to very low soil compaction without impacting on the superior tire strength.

VF 480/60R28 TL	145D		
VF 520/60R28 TL	149D		
VF 600/60R28 TL	157D		
VF 600/60R30 TL	158D		
VF 600/60R38 TL	168D	(165E)	
VF 650/60R38 TL	166D		
VF 650/60R38 TL	173D	(170E)	
VF 710/60R38 TL	171D		
VF 710/60R42 TL	173D	(170E)	
VF 750/70R44 TL	183D		

TM700

ProgressiveTraction®



Leading tractor manufacturers are constantly developing the middle range tractor lines, demanding extra traction performance and fuel efficiency from the tires, with limited space for larger tires. The TM700 ProgressiveTraction® is the answer. More efficient, more sustainable to produce more, with less.

380/70R28 TL	127D		
420/70R28 TL	133D		
480/70R28 TL	140D		
480/70R30 TL	141D		
480/70R34 TL	143A8	(143B)	
480/70R34 TL	155A8	(155B)	
480/70R38 TL	145D		
520/70R38 TL	150D		
580/70R38 TL	155D		
580/70R42 TL	158D		
620/70R42 TL	166D		

TM1000

HIGH POWER



The TM1000 High Power has been designed to equip the latest generation of high powered tractors. It is able to transfer to the ground the entire engine power, along with the torque driven by the latest breed of transmissions.

IF 600/70R30 TL	159D		
IF 650/60R34 TL	159D		
IF 650/65R38 TL	169D		
IF 710/70R42 TL	179D		
IF 900/60R42 TL	180D		
IF 710/65R46 TL	183D		

TM900

HIGH POWER



Good traction, excellent self-cleaning capability, comfort, low rolling resistance and low fuel consumption make the TM900 High Power the most advanced extra large agricultural radial tire in standard technology.

600/70R28 TL	157D	(154E)	
600/70R30 TL	158D	(155E)	
710/60R30 TL	162D	(159E)	
600/70R34 TL	160D	(157E)	
650/60R34 TL	159D	(156E)	
710/55R34 TL	164D	(161E)	
710/60R34 TL	164D	(161E)	
650/75R38 TL	169D	(166E)	
650/85R38 TL	173D	(170E)	
800/70R38 TL	178D	(175E)	
900/60R38 TL	178D	(175E)	
710/70R42 TL	173D	(170E)	
710/70R42 TL	179A8	*	
710/70R42 TL Harvester	173D	(170E)	
710/75R42 TL	175D	(172E)	
900/60R42 TL	180D	(177E)	

* = harvesting application

TM800



With its outstanding field and road performance, the TM800 has been developed for high power tractors. Excellent traction, superior load capability at high speeds, reduced soil compaction, ride comfort and excellent durability in every working conditions, all enhance the productivity of your farming operations.

320/65R18 TL	109A8	(109B)	
340/65R18 TL	113A8	(113B)	
440/65R24 TL	128D		
480/65R24 TL	133D		
540/65R24 TL	140D		
540/65R24 TL	146A8	**	
540/65R26 TL	141D		
440/65R28 TL	131D		
480/65R28 TL	136D		
540/65R28 TL	142D *		
540/65R28 TL	142D		
600/65R28 TL	147D		
540/65R30 TL	143D		
540/65R34 TL	145D		
600/65R34 TL	151D		
540/65R38 TL	147D		
600/65R38 TL	153D		
650/65R38 TL	157D *		
650/65R38 TL	157D		
710/70R38 TL	166D		
710/70R38 TL Sugar Cane	166D		
710/70R38 TL Forage	175D		
600/65R42 TL	154D		
650/65R42 TL	158D		
650/65R42 TL	165D	(168A8)	
TM800 HS			
540/65R28 TL	149D	(146E)	HS
600/65R28 TL	154D	(151E)	HS
540/65R30 TL	150D	(147E)	HS
540/65R34 TL	152D	(149E)	HS
600/65R34 TL	157D	(154E)	HS
540/65R38 TL	153D	(150E)	HS
650/65R38 TL	163D	(159E)	HS
650/65R38 TL	166D	(169A8)	HS
710/70R38 TL	171D	(168E)	HS

* = with ProgressiveTraction® tread pattern

** = for harvesting applications

TM700



The TM700 line guarantees outstanding performance. The combination of excellent traction in the field, self-cleaning properties, comfort and driveability on the road, make the first 70 series radial tire for agriculture the reference point for high quality tires.

240/70R16 TL	104A8	(104B)	
260/70R16 TL	109A8	(109B)	
280/70R16 TL	112A8	(112B)	
280/70R18 TL	114A8	(114B)	
280/70R20 TL	116A8	(116B)	
300/70R20 TL	110A8	(110B)	
320/70R20 TL	113A8	(113B)	
360/70R20 TL	120A8	(120B)	
380/70R20 TL	122A8	(122B)	
320/70R24 TL	116A8	(116B)	
360/70R24 TL	122A8	(122B)	
380/70R24 TL	125A8	(125B)	
420/70R24 TL	130A8	(130B)	
480/70R24 TL	138A8	(138B)	
480/70R26 TL	139A8	(139B)	
320/70R28 TL	119A8	(119B)	
360/70R28 TL	125A8	(125B)	
380/70R28 TL	127A8	(127B)	
420/70R28 TL	133D		
480/70R28 TL	140D		
480/70R28 TL	145D	(148A8)	
420/70R30 TL	134A8	(134B)	
480/70R30 TL	141D		
520/70R30 TL	145A8	(145B)	
480/70R34 TL	143A8	(143B)	
480/70R34 TL	155A8	(155B)	
520/70R34 TL	148A8	(148B)	
480/70R38 TL	145A8	(145B)	
520/70R38 TL	150D		
580/70R38 TL	155D		
580/70R42 TL	158D		
620/70R42 TL	166D		
TM700 HS			
480/70R30 TL	147D	(144E)	HS
520/70R30 TL	151D	(148E)	HS

PneuTrac®



The new PneuTrac® contains the best-in-class features of Trelleborg agricultural tires along with a new sidewall. The innovative "Omega" design of the sidewall helps the tire casing to sustain load, simultaneously providing flexibility and an extra-wide footprint at very low pressure, resulting in very low soil compaction.

VF 260/70R16 TL	110A8	(110B) *	NEW
VF 280/70R18 TL	116A8	(116B)	
VF 280/70R20 TL	118A8	(118B)	NEW
VF 380/70R24 TL	137A8	(137B) *	NEW
VF 420/70R28 TL	145A8	(145B)	NEW
VF 480/65R28 TL	148A8	(148B)	

* = in preparation

Tractor, combine and sprayer tires

Radial and Cross-ply range



TM600



Standard series tire with metric size designed for tubeless fitment.

Key features:

- optimal load capacity and traction
- maximum comfort on the road
- minimum soil compaction, maximum flotation
- excellent self-cleaning

210/95R16 TL	106A8	(106B)
210/95R18 TL	108A8	(108B)
280/85R20 TL	112A8	(109B) (11.2R20)
320/85R20 TL	119A8	(116B) (12.4R20)
250/85R24 TL	112A	(109B)
280/85R24 TL	115A8	(112B) (11.2R24)
320/85R24 TL	122A8	(119B) (12.4R24)
340/85R24 TL	125A8	(122B) (13.6R24)
380/85R24 TL	131A8	(128B) (14.9R24)
420/85R24 TL	137A8	(134B) (16.9R24)
280/85R28 TL	118A8	(115B) (11.2R28)
320/85R28 TL	124A8	(121B) (12.4R28)
340/85R28 TL	127A8	(124B) (13.6R28) *
380/85R28 TL	133A8	(130B) (14.9R28)
420/85R28 TL	139A8	(136B) (16.9R28) *
380/85R30 TL	135A8	(135B) (14.9R30) *
420/85R30 TL	140A8	(137B) (16.9R30) *
420/90R30 TL	147A8	(147B)
460/85R30 TL	145A8	(142B) (18.4R30)
380/85R34 TL	137A8	(137B) (14.9R34)
380/85R34 TL	142A8	(142B) (14.9R34)
420/85R34 TL	142A8	(139B) (16.9R34)
420/85R34 TL	147A8	(147B)
460/85R34 TL	147A8	(144B)
320/85R38 TL	129A8	(126B) (12.4R38)
340/85R38 TL	133A8	(130B) (13.6R38)
380/80R38 TL	142A8	(142B)
380/85R38 TL	144A8	(144B) (14.9R38)
380/95R38 TL	147A8	(147B) *
400/75R38 TL	138A8	(135B) (15.5R38)
420/85R38 TL	144A8	(141B) (16.9R38)
420/85R38 TL	149A8	(146B) *
460/85R38 TL	149A8	(146B) (18.4R38) *
480/80R38 TL	149A8	(149B) *
520/85R38 TL	155A8	(152B) (20.8R38) *
520/85R38 TL	155A8	(152B) (20.8R38) *
480/80R42 TL	151A8	(151B) (18.4R42) *
520/85R42 TL	157A8	(157B) (20.8R42) *
480/80R46 TL	158A8	(158B) (18.4R46)
520/85R46 TL	158A8	(158B) (20.8R46)
480/80R50 TL	159D	
480/80R50 TL Rice	159A8	(159B) *
480/95R50 TL	164A8	(164B) *

* = ProgressiveTraction® tread pattern

• = Available also in Heavy Duty version

TM100



The narrow tire specifically designed for row crop applications.

230/95R32 TL	128A8	(128B)
270/95R32 TL	136A8	(136B)
230/95R36 TL	130A8	(130B)
270/95R38 TL	140A8	(140B)
210/95R44 TL	120A8	(120B)
230/95R44 TL	134A8	(134B)
270/95R44 TL	142A8	(142B)
300/95R46 TL	148A8	(148B)
230/95R48 TL	136A8	(136B)
270/95R48 TL	144A8	(144B)
380/90R50 TL	151A8	(151B)
300/95R52 TL	151A8	(151B)
380/90R54 TL	152A8	(152B)

TM190



Suitable for many different operations and soil types.

Key features:

- top performer in long term usage both on field and on road
- reduced lug height offering very good performance on grassland
- high resistance to impacts

7.50R20	6 PR
9.5R20	8 PR
8.3R24	8 PR
9.5R24	107A8
12.4R36	124A8 (121B)

Marshland



Specialized line for use on waterlogged and marshy terrain. The extremely deep lugs, together with the structure of the casing, provide high traction and flotation.

380/85R38 TL	139A8	(139B)
420/85R38 TL	144A8	(144B)
460/85R38 TL	149A8	(149B)

TM150



TRAC TIRE TECHNOLOGY

The TM150 is Trelleborg's answer to the new generation of fertilizers and self-propelled high powered sprayers. In line with the VF standards, the tire can carry high loads while assuring low soil compaction, minimizing ruts and boosting crop yields.

VF 380/90R46 TL	173D
VF 380/105R46 TL	178D
VF 480/80R46 TL	177D
VF 520/85R46 TL	173D
VF 380/105R50 TL	179D
VF 480/80R50 TL	179D
VF 520/85R50* TL	177D
VF 380/105R54* TL	178D

* = in preparation

TM3000

TRAC TIRE TECHNOLOGY



The TM3000 is Trelleborg's answer to the latest and future generation of harvesters, combines and spreader machines. Matching sustainable and precision farming approaches, the TM3000 is the right choice to boost productivity.

VF 1000/50R25 TL	184D	*
VF 620/70R26 TL	CFO	173A8
VF 750/50R26 TL		169D
VF 750/65R26 TL	CFO	177A8 (177B)
650/75R32 TL		172A8
IF 800/65R32 TL	CFO	178A8
IF 800/70R32 TL	CFO	182A8
IF 900/65R32 TL	CFO	191A8 (191B)
VF 1050/50R32 TL		198D
IF 800/70R38 TL	CFO	187A8

* = spreader

• = for grain cart application also

TM2000



Radial tire for harvesting machines, result of the most advanced technology of Trelleborg experience in agricultural tires.

620/75R26 TL	166A8	(23.1R26)
650/75R32 TL	172A8	(24.5R32)
710/75R32 TL	177A8	
800/65R32 TL	178A8	(30.5LR32)
900/60R32 TL	181A8	

TM90



The Trelleborg TM90 offers a complete range of sizes for tractors up to 160hp. Engineered as a tubeless tire, the new R-1 tread pattern can be used in a variety of applications, both in the field and on the road.

8-16 TT	6 PR	91A8 CN
8-18 TT	6 PR	94A8
8.3-20 TT	6 PR	96A8 CN
11.2-20 TT	8 PR	111A8
11.8-20 TT *	8 PR	111A8
8.3-24 TT/TL	8 PR	105A8
9.5-24 TT/TL	8 PR	112A8
11.2-24 TT/TL	6 PR	110A8
12.4-24 TT/TL	8 PR	121A8
12.4-24 TL	12 PR	124A8 (128A6)
13.6-24 TT/TL	8 PR	123A8
14.9-24 TT/TL	8 PR	128A8
16.9-24 TT *	8 PR	133A8
16.9-24 TL	12 PR	136A8 (140A6)
14.9-26 TL	8 PR	129A8
16.9-26 TL Harvester	10 PR	137A6
12.4-28 TT	8 PR	123A8
13.6-28 TT/TL	8 PR	125A8
13.6-28 TL	12 PR	130A8 (134A6)
14.9-28 TT/TL	8 PR	130A8
14.9-28 TL	12 PR	134A8 (138A6)
16.9-28 TL	8 PR	135A8
14.9-30 TL	8 PR	131A8
16.9-30 TT/TL	8 PR	137A8
18.4-30 TT/TL	8 PR	139A8
18.4-30 TL	12 PR	145A8 (149A6)
16.9-34 TT/TL	8 PR	139A8
18.4-34 TT/TL	8 PR	142A8
18.4-34 TL	12 PR	146A8 (151A6)
12.4-36 TT/TL	8 PR	127A8
12.4-36 TL	12 PR	131A8 (135A6)
15.5-38 TT/TL	8 PR	129A8
16.9-38 TT/TL	8 PR	141A8
18.4-38 TT	8 PR	143A8
18.4-38 TL	12 PR	149A8 (153A6)
20.8-38 TL	12 PR	152A8 (156A6)

* = in preparation

T414



Twin Tractor. The tire range ideal for tractors and harvesters.

Key features:

- increased output from tractors and pulling machines
- maximum traction
- excellent self-cleaning

400/55-17.5 TL	125A8	(122B)
600/55-26.5 TL	148A8	(145B)
600/55-30.5 TL	150A8	(147B)
600/60-30.5 TL	153A8	(150B)
800/55-30.5 TL	172A8	(168B)
710/65-38 TL	162A8	(158B)
850/50-38 TL	163A8	(160B)
850/60-38 TL	175A8	(172B)
850/55-42 TL	161A8	(157B)

Implement tires

Cross-ply range



T423



T404



T421



T478



Twin Implement. Complete range of low ground pressure tires for machines and implements in the most severe and heavy agricultural service.

Key features:

- large ground contact area for minimum soil compaction
- low ground pressure
- low rolling resistance on soft ground
- good lateral stability

280/60-15.5	TL	115A8	T421
280/60-15.5	TL	125A8	T421
280/60-15.5		128A8	T478
400/45-15.5	TL	116A8	T423
400/60-15.5	TL	145A8	T404
400/60-15.5	TL	148A8	T404
400/60-15.5	TL	145A8	T478
420/55-17	TL	133A8	T421
420/55-17	TL	145A8	T421
400/55-17.5		131A8	T404
400/55-22.5	TL	147A8	T404
500/45-22.5	TL	146A8	T404
500/60-22.5	TL	155A8	T404

500/60-22.5	TL	155A8	T421
560/45-22.5	TL	154A8	T404
560/60-22.5	TL	167A8	T404
600/50-22.5	TL	156A8	T404
600/50-22.5	TL	156A8	T423
600/50-22.5	TL	165A8	T404
600/50-22.5	TL	168A8	T404
710/40-22.5	TL	158A8	T404
400/60-26.5		147A8	T404
600/55-26.5	TL	166A8	T404
600/55-26.5	TL	166A8	T421
600/55-26.5	TL	173A8	T421

710/45-26.5	TL	169A8	T404
710/45-26.5	TL	169A8	T423 MK2
800/40-26.5	TL	172A8	T404
800/40-26.5	TL	172A8	T423 MK2
650/65-30.5	TL	173A8	T404
710/50-30.5	TL	175A8	T404
710/50-30.5	TL	175A8	T423
750/60-30.5	TL	178A8	T404
800/45-30.5	TL	178A8	T404
800/45-30.5	TL	178A8	T423
850/50-30.5	TL	179A8	T404

T421



T428



T404



T423



T440



Twin Garden Tractor. Low ground pressure tire especially designed for grass and other delicate surfaces.

Key features:

- maximum flexibility both on hard and soft ground
- great soil respect for minimum compaction and no track formation

400/55-17.5	TL	108A8	T404
400/55-22.5	TL	111A8	T404
600/60-30.5	TL	142A8	T404

Twin Ampt. Agricultural multi purpose and low ground pressure tires for field and road.

Main applications:

- use at speeds up to 40 mph as well as in heavy duty applications
- for machines and implements with high road use

620/50B22.5	TL	160D	T423
650/45B22.5	TL	160D	T440
710/40B22.5	TL	161D	T423
620/55B26.5	TL	166D	T421
650/55B30.5	TL	168D	T428
750/50B30.5	TL	173D	T428
850/45B30.5	TL	176D	T423

Transport equipment

Radial range



HF1000



Twin Radial



The VF and steel belted HF1000 has been designed for manure tankers, big forage wagons and slurry tankers. It delivers excellent flotation and self-cleaning features in the field and a comfortable ride, easy handling and high stability on the road.

VF 750/60R30.5 IMP	TL	187D
VF 800/60R32 IMP	TL	191D

Radial implement tire perfect in all working conditions.

Key features:

- great comfort and even wear
- excellent self-cleaning
- reduced fuel consumption
- excellent ground care

500/60R22.5	TL	155D
560/60R22.5	TL	161D
580/65R22.5	TL	159D
600/50R22.5	TL	159D
600/55R26.5	TL	165D
680/55R26.5	TL	171D
710/50R26.5	TL	170D
650/65R30.5	TL	176D
750/60R30.5	TL	181D
850/50R30.5	TL	182D
800/60R32	TL	185D

Implement Standard and High Speed tires

Cross-ply range



AW305



AF302



T452



AW309 Flotation



T306



RT HS



Tubeless and load/speed index rated, recommended for trailers.

Key features:

- soft ground contact
- low rolling resistance on road transport
- wide range of sizes

RT HS: high speed tire for general purpose use, both for implements and trailers.

10.0/80-12	TL	8 PR	AW305
10.0/80-12	TL	10 PR	AW305
200/95-12	TL	101A8	AF302
260/90-13	TL	121A8	AF302
260/70-15.3	TL	126A8	AW305
260/70-15.3	TL	131A8	AW305
300/80-15.3	TL	123A8	T452
300/80-15.3	TL	141A8	T452
300/80-15.3	TL	132A8	AW305
300/80-15.3	TL	141A8	AW305
320/80-15.3	TL	145A8	AW305
180/90-16	TL	100A8	AF302
190/90-16	TL	108A8	AF302
200/90-16	TL	111A8	AF302

210/95-16	TL	120A8	AF302
260/70-16	TL	134A8	AW305
340/55-16	TL	140A8	AW305
340/55-16	TL	140A8	AW309
360/65-16	TL	148A8	AW305
360/70-16	TL	137A8	AW305
380/55-17	TL	138A8	AW305
380/55-17	TL	138A8	AW309
420/55-17	TL	143A8	T452
480/45-17	TL	146A8	AW305
480/45-17	TL	150A8	AW309
500/50-17	TL	149A8	AW309
520/50-17	TL	159A8	T306
500/55-20	TL	150A8	AW309

Forestry tires

Cross-ply range



T404



T428



T418 Forestry Skidder



T418 T418 High Power

It is specifically designed for log skidding service with maximum penetration and tear resistance. It provides long tire life under the most severe operating conditions. The armored plies protect the carcass against stumps, boulders and rocks.

23.1-26	TL	16 PR
28L-26	TL	20 PR
28L-26	TL	26 PR
24.5-32	TL	16 PR
30.5L-32	TL	20 PR
30.5L-32	TL	26 PR
30.5L-32	TL	32 PR*
DH 35.5L-32	TL	24 PR
DH 35.5L-32	TL	30 PR*

* T418 High Power

T421



T480



Twin Forestry. The advanced tire technology applied to develop performance for the forestry range.

Key features:

- excellent stability and comfort
- reliability
- best possible pull force and durability

500/45-22.5	129A8	T404	FS
500/60-22.5	144A8	T421	SB
600/60-30.5 TL	153A8	T414	FS
600/50-22.5	LS2 149A8	T480	SB
650/45-22.5	LS2 150A8	T440	SB
710/40-22.5	LS2 161A8	T480	SB
710/40-24.5	LS2 163A8	T440	SB
710/40-24.5	LS2 163A8	T480	SB
600/55-26.5	LS2 165A8	T440	SB
600/55-26.5	LS2 165A8	T480	SB
710/45-26.5	LS2 168A8	T440	SB

710/45-26.5	LS2 168A8	T480	SB
710/45-26.5	LS2 173A8	T480	SB
750/55-26.5	LS2 182A8	T440	SB
750/55-26.5	LS2 182A8	T480	SB
800/40-26.5 TL	LS2 170A8	T440	SB
800/40-26.5 TL	LS2 170A8	T480	SB
780/50-28.5	LS2 182A8	T480	SB
750/45-30.5	LS2 173A8	T428	SB
600/65-34 TL	LS2 163A8	T440	SB
710/55-34 TL	LS2 167A8	T440	SB

T410



Agro Forest. Designed for mixed forestry and agricultural service.

Key features:

- high traction
- good load capability
- great durability in agricultural operations

320/85-24	127A8 (124B)
380/85-24	137A8 (134B)
380/85-24 TL	143A8 (140B)
380/85-28	139A8 (136B)
420/85-28	144A8 (141B)
460/85-30	150A8 (147B)
420/85-34	147A8 (144B)
420/85-34 TL	153A8 (150B)
460/85-34	152A8 (149B)
420/85-38	149A8 (146B)
460/85-38	154A8 (151B)
520/85-38	160A8 (157B)

Agro Industrial tires

Radial and cross-ply range



TH400



Radial line designed for telescopic handlers, backhoes and compact loaders.

The TH400 represents the perfect solution both for farming and for light industrial applications.

Key features:

- great stability
- excellent safety
- maximum resistance to stress and cuts
- superior traction
- outstanding self-cleaning

11LR16	TL	IND	130A8		
340/80R18	TL	IND	143A8 (143B)	(12.5-18)	
400/70R18	TL	IND	147A8 (147B)	(15.5/70-18)	
400/70R20	TL	IND	149A8 (149B)	(16.0/70-20)	
400/70R24	TL	IND	152A8 (152B)	(16.0/70-24)	
440/80R24	TL	IND	161A8 (161B)	(16.9-24)	
460/70R24	TL	IND	159A8 (159B)	(17.5L-24)	
500/70R24	TL	IND	164A8 (164B)	(19.5L-24)	
480/80R26	TL	IND	160A8 (160B)	(18.4-26)	
440/80R28	TL	IND	156A8 (156B)	(16.9-28)	

TH500



The Trelleborg TH500 tire perfectly matches the requirements of telehandlers and backhoes operating on hard surfaces. Both on the road and in the yard the TH500 delivers exactly the performance and reliability you need from a tire.

The TH500 tread design is closed in the center to deliver long tire life and on road performance while its open shoulder construction ensures excellent self-cleaning capabilities.

340/80R18*	TL	IND	143A8 (143B)	(12.5-18)	
400/70R20*	TL	IND	149A8 (149B)	(16.0/70-20)	
460/70R24	TL	IND	159A8 (159B)	(17.5L-24)	
500/70R24	TL	IND	164A8 (164B)	(19.5L-24)	

* = in preparation

MPT100



Steel belted tire designed for multi-purpose off-road trucks. The MPT100 stands out for its great wear resistance, stability and comfort while running on or off the road. In the field it delivers excellent traction.

425/75R20	TL	IND	158G	NEW
405/70R20	TL	IND	136G	NEW
445/65R22.5	TL	IND	160G	NEW

Rear tractor industrial tires

Cross-ply range



T459



T440 EXC



T480 EXC



Recommended for excavators, loaders and for machines in urban and industrial operations.

Key features:

- good grip
- braking capability on hard surfaces

600/50-22.5	TL	173A8	T480 EXC
650/45-22.5	TL	175A8	T440 EXC
710/40-22.5	TL	176A8	T480 EXC
620/60B34	TL	175A8	T459
600/65-34	TL	175A8	T440 LD SB

Light service tires

farming, industrial and green areas

Cross-ply range



Wide range of tires from 4" to 15" developed for farming, industrial and green area applications. Also available as complete wheel systems.



Complete wheel range for agricultural and forestry tires



Agricultural Wheels



Trelleborg Wheel Systems produces high quality wheels for forestry, agricultural, industrial and earth moving applications with diameters from 3 to 54 inches.


DU0500 mounted on the tractor wheel



The DU0500 is the Trelleborg offer for dual tractor tires.

- Easy to maintain and service
- Easy to mount and demount
- Attached rim and drum for easy handling
- Painted in the original color of the tractor

THK



Trelleborg High Knurling - THK handles high stress and extreme torque, enabling tractors to work at maximum efficiency and productivity.

Together with Trelleborg Extra Large tires, the THK represents a system that meets all requirements.

The knurling has been increased by 50% compared to the standard version. This, combined with the special black paint, maximizes the friction characteristics of the rim when the tire is fitted.



Printed on
recycled paper



Discover our website
trelleborg.com/wheels/us

Follow us



Trelleborg Wheel Systems Americas Inc.
570 Trelleborg Drive
Spartanburg, SC 29301
Toll Free Number: 1-866-633-8473
www.trelleborg.com/wheels/us

